


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20	
© COPYRIGHT 20		ALL RIGHTS RESERVED.			
PART NUMBER		REVISION		DESCRIPTION	
1893217-1		B		MINI APPLICATOR, LOOSE PIECE VERSION	
7-1893217-1		A		APPLICATOR DRAWER	

LOC	DIST	REVISIONS					
AP	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RELEASED	01APR2009	JL J	CCL
		B		ECO-20-000868	17JAN2020	AG	DA

CRIMP DATA				
TERMINAL DESCRIPTION FEMALE TERMINAL				
DISC LETTER	CRIMP HEIGHT		WIRE SIZE	STRIP LENGTH
A	-		-	-
B	-		-	-
C	3,75 + 0,05		6,00 MM ²	12,50 ± 0,50 MM
D	-		-	-
CRIMPER	CRIMP WIDTH	TYPE	APPLICATOR FEED	INSTRUCTION SHEET
WIRE	4,00	"U"	-	8024
INSULATION	-	-		
INSULATION RANGE		WIRE RANGE 6,00 MM ²		GAUGE 571319-1
PARA APLICAR TERMINAL: (TO USE TERMINAL)				
94818001				
ROCKWELL CUSTOMER CODE				



NOTE :

 RECOMMENDED SPARE PARTS

4 GREASE BEARING SURFACES LIGHTLY

5 MAGNET, ITEM 53, MUST BE ORIENTED
CORRECTLY IN ORDER TO PROPERLY ACTUATE
THE COUNTER.

6- APPLICATOR TO BE USED ON BENCH
TERMINATORS ONLY.

7- UNLESS SPECIFIED OTHERWISE TORQUE
VALUES SHALL BE USED PER DOCUMENT,
101-35000.

-	2	18025-2	Whaser, SPGR Lock, REG M4	57
-	1	18023-3	Screw,Cap, Socket	56
-	2	18023-3	Screw,Cap, Socket	55
-	1	2076888-1	Rear Applicator	54
-	1	994969-1	Magnet, Rare	53
-	1	18032-1	Screw, Socket Head	52
-	1	994970-2	Counter,Magnetic	51
-	2	1707368-4	Spacer, Applicator Guard	50
-	1	22480-5	Washer, Spring Lock	49
4	4	18024-1	Screw, Socket, Button Head	48
-	1	1707784-1	Lock, Pawl	47
-	1	3-22279-7	Spring, Compression	46
-	1	1707785-1	Lock,Lever Release	45
-	1	1707755-2	Knob	44
-	1	1707783-1	Lock, Support	43
-	1	3-992946-2	Pin Dowel	42
-	2	2-18024-0	Screw, Socket, Button Head	41
-	2	992946-3	Pin Dowel	40
-	1	1707824-1	Base Plate	39
-	1	9-196804-2	Microswitch	38
-	2	18023-6	Screw,Cap, Socket Head	37
-	1	1707826-1	Block, Guide Stop Screw	36
-	2	1-18023-3	Screw,Cap, Socket Head	35
1	1	9-18023-4	Screw,Cap, Socket Head	34
1	1	1707779-1	Knob	33
2	2	18023-4	Screw,Cap, Socket Head	32
1	1	624887-4	Applicator Guard	31
1	1	1707825-4	Guide Block	30
1	1	2076046-1	Anvil	29
1	1	2076047-4	Support, Terminal	28
1	1	2076048-4	Cover	27
1	1	18030-4	Nut, Hex,Reg.Metric	26
1	1	197241-2	Spring Positioner	25
-	1	1707780-2	Right Guide	24
-	1	1707781-2	Left Guide	23
3	4	18023-5	Screw,Cap, Socket Head	22
-	1	1707831-2	Applicator Guard	21
-	1	1707541-1	Cap, Ram	20
-	1	571417-4	Striper	19
-	10	1-18023-2	Screw,Cap, Socket Head	18
-	1	3-18023-7	Screw,Cap, Socket Head	17
1	1	2076045-1	Wire Crimper	16
-	1	690191-1	Plug Nylon	15
-	1	18032-8	Screw Set, Socket, Flat Point	14
-	1	23241-6	Ball Steel	13
-	1	690603-1	Spring Assist.	12
-	1	690170-1	Compression Spring	11
-	1	23030-1	Screw, Cap, Socket Head	10
-	4	18025-3	Washer, Spring Lock	09
-	4	2-18023-4	Screw, Cap, Socket Head	08
-	1	1707823-1	Housing, Applicator	07
-	1	1707115-1	Ram	06
-	REF.	690125-1	Washer Flat	05
-	1	690124-1	Washer Ram	04
-	1	690223-2	Spacer, insulation disc	03
-	1	3-571001-0	Wire Disc	02
-	1	690212-1	Post Ram	01
7- -	-	PART NUMBER	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. JODAR 01APL2009	TE Connectivity									
		CHK C. MENEGHIN 01APL2009										
		APVD C. LIMA 01APL2009										
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME MINI APLICADOR ESPECIAL (SPECIAL APPLICATOR MINI) LOOSE PIECE								
		0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±.										
MATERIAL		FINISH		PRODUCT SPEC -		APPLICATION SPEC -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-		-		WEIGHT -		A200779		C-1893217		-		
CUSTOMER DRAWING								SCALE	2.5	SHEET	OF	REV
												B