

4


3

2





1

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS			B2	REVISED (ECR-16-009958)	02/MAY/11	SJ	HG
			C	REVISED (ECR-23-166035)	23/MAR/23	CI	KT




SECTION A1-A1



<TABLE 1>					
TYPE	PART NO.	WIRE SIZE(mm ²)	Insulation DIA(mm)	Applicable WIRE	FINISH
MTII	0-963902-1	0.2~0.5	1.15~1.6	AVSSXF 0.5 Max	CuSn4
	0-963902-3				CuSn4(GOLD)
	0-963904-1	0.5~1.0	1.4~2.1	AVSSXF 0.85 Max	CuSn4
	0-963904-3				CuSn4(GOLD)
JPT	1-962915-1	0.5~1.0	2.1 Max	AVSSXF 0.85 Max	CuSn4
	1-962915-3				CuSn4(GOLD)
	1-962916-1	1.0~2.5	3.0 Max	AVSS 2.0 Max or FLR 2.5 Max	CuSn4
	1-962916-3				CuSn4(GOLD)



ISOMETRIC VIEW



<TABLE 2>			
TYPE	PART NO.	WIRE INSULATION DIAMETER(mm)	COLOR
MTII	964971-1	1.2~1.6	RED
	963530-1	1.4~1.9	GRAY
	964972-1	1.9~2.1	YELLOW
	963531-1	CAVITY PLUG	WHITE
JPT	828904-2	1.2~2.1	BLUE
	828905-1	2.2~3.0	WHITE
	828922-1	CAVITY PLUG	NATURAL

NOTE
1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. APPLIED PLUG P/N: X-1897009-X
APPLIED WIRE COVER P/N: X-1897015-X
3. APPLICABLE TAB CONTACT P/N: TABLE 1
4. APPLICABLE WIRE SEAL P/N: TABLE 2

B2	CAP HSG FOR HYB 26P	PA66-GF30	C	GRAY	1897013-3
	CAP HSG FOR HYB 26P	PA66-GF30	C	BLACK	1897013-2
	DESCRIPTION	MATERIAL	COLOR	P/N	

TE TE Connectivity

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN SJ OHG	 TE Connectivity							
		CHK JW JUNG								
DIMENSIONS: MM		APVD HG OHG	NAME							
 3rd ANGLE PROJECTION		PRODUCT SPEC	CAP HSG FOR MTII/JPT SEALED 26P CONN'R							
		APPLICATION SPEC								
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
SEE TABLE			A2		C- 1897013					
		CUSTOMER DRAWING			SCALE	2:1	SHEET	1 OF 1	REV	C