

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.





LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN
			D	REVISED PER ECO-08-007327	05SEP08	BM
						APVD
						WM





1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.

2. MATERIAL: HOUSING - POLYPHENYLENE OXIDE (BLACK).

TERMINAL - HIGH STRENGTH COPPER ALLOY PLATED WITH .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, .000030 MIN TOTAL ON MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.

3. WIRE SIZE: 24 OR 26 AWG SOLID OR 24 AWG 7 STRANDS OF COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. PATTERSON 24AUG06		<div>Tyco Electronics Corporation Harrisburg, PA 17105-3608</div>					
		CHK W. MILLHIMES 24AUG06							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME EMI PLUG ASSEMBLY, 50 POSITION, SCREW LOCK, B-SLOT, CHAMP (4-40 HOLES)					
		APVD W. MILLHIMES 24AUG06							
		PRODUCT SPEC —		SIZE A2					
		APPLICATION SPEC —							
MATERIAL		FINISH		CAGE CODE 00779		DRAWING NO C-1888616		RESTRICTED TO —	
				CUSTOMER DRAWING				SCALE 2:1	
						SHEET 1 of 1		REV D	