





LOC	LIST	REV. NO.	DESCRIPTION	DATE	DWN	APVD
J		A	RELEASED	09DEC08	KK	HY
		A1	REVISED ECR-09-014331	10SEP12	KK	HY
		A2	REVISED ECR-17-008680	15JUN17	TA	TK



- 本製品は、別番のコンポーネントと組合せて使用する。
 - 取扱説明書 NO: 411-78268
 - 組合せ相手型番: 取扱説明書を参照のこと。
 - 嵌合相手代表型番: 取扱説明書を参照のこと。
 - 適用端子: TABLE-1参照
 - 0.13-0.35mm²電線のみ適用。
- THIS PRODUCT IS USED STACK WITH ANOTHER COMPONENTS.
 - HANDLING OF THIS PART SHOULD FOLLOW INSTRUCTION SHEET NO.411-78268.
 - COMPONENTS NUMBER OF STACKING;REFERENCE TO INSTRUCTION SHEET.
 - MATING CONNECTOR PART(TYPICAL);REFERENCE TO INSTRUCTION SHEET.
 - APPLIED TERMINAL:SEE TABLE-1.
 - THIS POSITION APPLIED ONLY TO 0.13-0.35mm² WIRE.

		APPLIED TERMINAL P/N 適用端子 P/N	APPLICABLE WIRE RANGE 適用電線
SIGNAL 0.5	TIN	1827855-4	0.13-0.5mm ²
	TIN	1827855-1	
	GOLD	1903703-1	
	TIN	1827855-2	
	TIN	1827855-3	

PAPER BOX ダンボール箱	SOFT TRAY プラスチックトレイ	BLACK 1903883-9	1903883-2
		NATURAL 1903883-1	
OUTER 外装	INNER 内装	COLOR	PART NO.
PACKING STYLE 梱包形態			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: mm	DWN R. KATO	09DEC08
		CHK R. KOMIYAMA	09DEC08
		APVD H. YAMAGAMI	09DEC08
		PRODUCT SPEC	108-78437
		APPLICATION SPEC	
MATERIAL PBT	FINISH SEE TABLE	WEIGHT 1.51 g	SIZE A1
		CUSTOMER DRAWING	SCALE 5:1

RESTRICTED TO

0.5 16POSITION PLUG HOUSING ASSY
STACKING TYPE

00779 ©=1903883

SHEET 1 OF 1 REV A2