





LOC		DIST		REVISIONS			
P	LYN	DATE	OWN	APVD			
L1		09MAR2023	IT	WH	REVISED PER ECR-23-166294		




- MATERIAL:
 - HOUSING: PBT POLYESTER, BLACK, UL 94V-0.
 - TERMINALS: 0.35 THICK PHOSPHOR BRONZE PLATED WITH 1.27um MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2.0um MINIMUM THICK MATTE TIN IN ACTION PIN COMPLIANT PIN TERMINAL AREA OVER 1.27um MINIMUM THICK NICKEL UNDERPLATE.
 - SHIELD: 0.25 THICK COPPER ALLOY PLATED WITH 1.27um MINIMUM THICK NICKEL GROUNDING CLIP.
 - GROUNDING CLIP: 0.25 THICK COPPER ALLOY PLATED WITH 1.27um MINIMUM THICK NICKEL LIGHT EMITTING DIODE (LED): DIFFUSED EPOXY LENS, 12.95 CARBON STEEL WIREFRAME LEADS PREPLATED WITH 8.89um THK. TIN/COPPER OVER 2.03um THK. SILVER OVER 1.02um COPPER OVER 3.56um THK. NICKEL OVER 1.02um THK. COPPER UNDERPLATE.
 - LED ACTION PIN - COMPLIANT PIN CONTACTS: 0.3 THICK BRASS PLATED WITH 2um MINIMUM MATTE TIN OVER 1.27um MINIMUM NICKEL UNDERPLATE.
 - JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
 - MAXIMUM PIN LENGTH 3.40 FROM TOP SURFACE OF PC BOARD.
- 3/4 FINISHED PLATED THRU HOLE DIAMETER - ANNULAR RING DIAMETER 1.3 TO 1.5
 5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
 6 DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN
 7 CONTACTS ARE NOT INTENDED TO BE ALIGNED WITH EACH OTHER
 8 SUGGESTED OPERATING CURRENT FOR LEDS IS 20 mA
 9 PCB THROUGH HOLES FOR LED #1 AND LED #4 ARE NOT REQUIRED FOR 1888653-5,6, 1-1888653-1.
 10 THE PN 1-1888653-1 LED DOMINANT WAVELENGTH: GREEN 525nm TYP. YELLOW 590nm TYP.


ATCA PANEL AND PRINTED CIRCUIT BOARD ASSEMBLY LAYOUT




AMC PANEL AND PRINTED CIRCUIT BOARD ASSEMBLY LAYOUT



1888653-5,-6
 (REPRESENTATION OF -5,-6 SHOWN IN THIS VIEW ONLY)



1-1888653-1
 SCALE 3:1



1-1888653-1
 SCALE 4:1

15.88	NONE	GREEN/YELLOW	GREEN/YELLOW	NONE	WITH GROUND CLIP	1-1888653-1 10
15.88	NONE	GREEN	YELLOW	NONE	WITH GROUND CLIP	1888653-9
15.88	YELLOW	GREEN	GREEN	GREEN	WITH GROUND CLIP	1888653-7
15.88	NONE	GREEN	GREEN	NONE	WITH GROUND CLIP	1888653-6
15.88	NONE	YELLOW	GREEN	NONE	WITH GROUND CLIP	1888653-5
15.88	YELLOW	YELLOW	GREEN	GREEN	WITH GROUND CLIP	1888653-4
15.88	GREEN	GREEN	YELLOW	YELLOW	WITH GROUND CLIP	1888653-3 (SHOWN)
15.88	GREEN	GREEN	GREEN	GREEN	WITH GROUND CLIP	1888653-2
16.13	GREEN	GREEN	GREEN	GREEN	WITHOUT GROUND CLIP	1888653-1
M DIM	LED #4 (LOWER-RIGHT)	LED #3 (UPPER-RIGHT)	LED #2 (UPPER-LEFT)	LED #1 (LOWER-LEFT)	DESCRIPTION	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm
 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ±
 1 PLC ±0.13
 2 PLC ±
 3 PLC ±
 4 PLC ±
 ANGLES ±1°
 MATERIAL: SEE NOTE 1
 FINISH:


DWN: L.A.MAYER 19OCT2006
 CHG: J.WESTMAN 19OCT2006
 APVD: S.FLICKINGER 19OCT2006
 NAME: STACKED MOD JACK ASSEMBLY, 2 X 1, 8 POSN, RJ45, SHIELDED, PANEL GROUND, OFFSET, CAT 5e
 PRODUCT SPEC: 108-1854
 APPLICATION SPEC: 114-2160
 WEIGHT: -
 CUSTOMER DRAWING:

STE TE Connectivity
 SIZE: A1
 CAGE CODE: 00779
 DRAWING NO: 1888653
 SCALE: 4:1
 SHEET: 1 OF 2
 REV: L1


LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		




**ATCA PANEL AND
PRINTED CIRCUIT BOARD LAYOUT**




**AMC PANEL AND
PRINTED CIRCUIT BOARD LAYOUT**



**PC BOARD LAYOUT
(COMPONENT SIDE)**



**LED CURRENT DIAGRAM
FOR 1-1888653-1**



**DETAIL B
SCALE 12:1
PLATED PADS REQUIRED FOR
1888653 -2, 3, -4, -5, -6 & -7 (PRODUCT WITH
GROUNDING CLIPS)**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN L.A.MAYER 19OCT2006	TE Connectivity
DIMENSIONS: mm		CHK J.WESTMAN 19OCT2006	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.13 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		APVD S.FLICKINGER 19OCT2006	NAME STACKED MOD JACK ASSEMBLY, 2 X 1, 8 POSN, RJ45, SHIELDED, PANEL GROUND, OFFSET, CAT 5e
MATERIAL SEE NOTE 1		PRODUCT SPEC 108-1854	SIZE A1
		APPLICATION SPEC 114-2160	CAGE CODE 00779
		WEIGHT	DRAWING NO C=1888653
		CUSTOMER DRAWING	SCALE 6:1
			SHEET 2 OF 2
			REV L1