


1. MAXIMUM CABLE INSERTION LOSS: 2.3 dB (1300nm)
2. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.

SEE LABEL DETAIL.

MIL-T-29504/04 PIN TERMINI ARE INSTALLED IN POSITIONS v AND y OF THE MS27467 PLUG CONNECTOR.

- FILLER PLUGS INSTALLED IN ALL UNUSED POSITIONS OF MS27467 CONNECTOR.
- MOLDED BOOTS TO BE POLYURATHANE PER MIL-M-24041C, TYPE II.
- M39029/58-363 PIN CONTACTS INSTALLED IN POSITIONS m AND S. CONTACTS CRIMPED TO 20 AWG WIRE, MIL-W-22759/43.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
16		SEE REVISION SHEET	25JAN18	KG	DW



N (NORMAL)	56.00±1.00	1918961-2
N (NORMAL)	29.00±1.00	1918961-1
38999 SHELL KEYING DESIGNATION	L	PART NUMBER

DESIGN APPROVED THIS PRINT IS


PRELIMINARY

TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. GLATFELTER 02FEB2007	TE Connectivity	
DIMENSIONS: METERS		CHK J. SHIPE 23FEB2007		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BAECHTLE 23FEB2007	NAME CABLE ASSEMBLY, FO, 2 FIB, 62.5/125 38999 PLUG TO MS27467 PLUG (OLIVE DRAB)	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC - APPLICATION SPEC -	SIZE A1	
MATERIAL -		WEIGHT 0	DRAWING NO 00779	
FINISH -		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE NTS		SHEET 1 OF 3
				REV 16

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
—	—	SEE SHEET 1	—	—

ASSY	LABEL 1	LABEL 2	LABEL 3	LABEL 4
1	P50099R/J9 EOC	96550–01814–102 Rev J 78286 MOLDED C/A, FIB OPTIC	00779 XXXXXXXXXXXXXXXXX (MFR–1918961–1)	P708R/J708R AMCM CABIN DISC.
2	P50099R/J9 EOC	96550–01814–103 Rev J 78286 MOLDED C/A, FIB OPTIC	00779 XXXXXXXXXXXXXXXXX (MFR–1918961–2)	P708R/J708R AMCM CABIN DISC.

LABEL DETAIL 

DESIGN APPROVED THIS PRINT IS

PRELIMINARY

TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. GLATFELTER 22MAR2007	 TE Connectivity			
		CHK J. SHIPE 10APR2007				
DIMENSIONS: METERS	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 1 2 3 4 PLC ± ± ± ± ± ANGLES ± ±	APVD M. KADAR–KALLEN 10APR2007	NAME	CABLE ASSEMBLY, F0, 2 FIB, 62.5/125 38999 PLUG TO MS27467 PLUG (OLIVE DRAB) —		
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL —	FINISH —	WEIGHT 0	SIZE A1	CAGE CODE 00779	DRAWING NO 1918961	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 2	OF 3	REV 16

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

REVISION	DESCRIPTION OF CHANGES	DATE	APPROVAL
2	CHANGE TO MOLDED BOOTS. ADD DIMENSIONS 2.75 MAX AND 3.60 MAX. ADD NOTE 6. ADD LABEL DETAIL ON SHT 2.	26MAR07	J. SHIPE
3	ADD POLYURETHANE TUBING. ADD NOTE 7.	11APR07	J. SHIPE
4	REVISE M TO <u>m</u> NOTE 7 AND CHANGE HOLE LOCATION.	09APR08	J. SHIPE
5	CHANGE LABEL 2, SIKORSKY P/N REVISION CHANGED FROM F TO H.	23DEC08	J. SHIPE
6	REVISE LABEL DETAIL ON SHEET 2. REMOVE PARENTHESIS FROM LABEL 2 AND LABEL 3. CHANGE LABEL 3 FROM: 1918961-X TO: (MFR-1918961-X).	23FEB12	D.KIRSCH
7	CHANGE SIKORSKY LABEL 2 REVISION FROM: H TO: J.	03DEC14	D.KIRSCH
8	ECR-15-011915	26AUG15	D.WERTMAN
15	ECR-17-010969	14AUG17	D.WERTMAN
16	ECR-18-000867	25JAN18	D.WERTMAN

DESIGN APPROVED

THIS PRINT IS

PRELIMINARY

TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
METERS

0

1

2

3

4

PLC

PLC

PLC

PLC

PLC

±

±

±

±

±

-

-

-

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0

1

2

3

4

PLC

PLC

PLC

PLC

PLC

±

±

±

±

±

-

-

-

-

-

MATERIAL

-

FINISH

-

DWN
K. GLATFELTER
CHK
J. SHIPE
APVD
M. KADAR-KALLEN

10APR2007
10APR2007
10APR2007

NAME

CABLE ASSEMBLY, F0, 2 FIB, 62.5/125
38999 PLUG TO MS27467 PLUG (OLIVE DRAB)

PRODUCT SPEC

APPLICATION SPEC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

0

A1

00779

1918961

-

CUSTOMER DRAWING

SCALE
NTS

SHEET
3

OF
3

REV
16

4805 (1/15)