




LOC	DIST	REVISIONS					
IN	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		REV PER ECR-08-004125	21FEB2008	HM	DF
		A1		REV PER ECO-08-005762	06MAR2008	HM	DF
		B		REV PER ECO-09-005747	06MAR2009	HM	DF
		B1		REV PER ECO-09-010497	30APR2009	HM	DF




- 1 HOUSING: PCT, COLOR - BLACK
CONTACTS:BRASS
SOLDER CLIP: BRASS
- 2 SOLDER CLIP: TIN OVER NICKEL
- 3 CONTACT: TIN IN MATING AREA AND TIN
IN SOLDER TAIL AREA ALL OVER NICKEL
- 4 DATUMS AND BASIC DIMENSIONS ARE ESTABLISHED BY THE CUSTOMER
- 5 ALLOW FOR OVER PRINTING ON PC BOARD
- 6 SOLDER PASTE VOLUME PER LAYOUT
SOLDER TAIL = 1.95mm³ SOLDER CLIP = 3.77mm³
SOLDER PASTE THICKNESS CAN CHANGE BASED ON APERTURE SIZE
BUT SHOULD NOT VIOLATE 0.15mm MIN THICKNESS.
- 7 THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING
- 8 PRELIMINARY - NOT FOR PRODUCTION




KEYING CODE "A"
SCALE 4:1






KEYING CODE "B"
SCALE 4:1



KEYING CODE "C"
SCALE 4:1




KEYING CODE "D"
SCALE 4:1



2.90	15.50	2.70	3.95	20.40	KEYING CODE "D"	1927688-4
2.90	16.50	2.70	3.94	20.38	KEYING CODE "C"	1927688-3
2.90	13.50	1.20	5.45	18.90	KEYING CODE "B"	1927688-2
2.30	14.50	2.15	4.50	19.85	KEYING CODE "A"	1927688-1
E	D	C	B	A	KEYING CODE	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN H. MOLL 25JUL2007		Tyco Electronics	
mm		0 PLC ±		CHK D. FRY 25JUL2007		Harrisburg, PA 17105-3608	
MATERIAL		1 PLC ±		APVD J. MYER 25JUL2007		NAME	
		2 PLC ±				PRODUCT SPEC	
		3 PLC ±				APPLICATION SPEC	
		4 PLC ±				SIZE CAGE CODE DRAWING NO	
		ANGLES				A100779C=1927688	
		FINISH				RESTRICTED TO	
		SEE TABLE				-	
						CUSTOMER DRAWING	
						SCALE 3:1 SHEET 1 OF 2 REV B1	



THIS DRAWING IS A CONTROLLED DOCUMENT FOR THE TYPICO ELECTRONICS CORPORATION NO REPRODUCTION OR DISSEMINATION OF THIS DRAWING WITHOUT THE WRITTEN PERMISSION OF THE TYPICO ELECTRONICS CORPORATION		DWN 25JUL2007 CHN MOLL 25JUL2007 D FRY 25JUL2007 APUR MYER 25JUL2007		tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLOC ±.1 3 PLOC ±.1 3 PLOC ±.1 4 PLOC ±.1 4 PLOC ±.1 ANGLES ±.1°		NAME HEADER ASSY, 1x6, UNSEALED, LOW PROFILE, SMT, GET	
MATERIAL -		APPLICATION SPEC -		SIZE A 100779	
FINISH SEE TABLE		WEIGHT -		DRAWING NO 1927688	
CUSTOMER DRAWING		SCALE 3:1		SHEET 2 OF 2	
REV B		REV B		REV B	