






[TABLE 1]


TYPE	P/N	WIRE SIZE	MATERIAL/FINISH
.090	0-368088-1	0.3~0.5	CuNiSi ALLOY PRE-TIN
	0-368087-1	0.85~1.25	
	0-368086-1	2.0	



ISO VIEW



SECTION A-A



NOTE

1. GENERAL TOLERANCE: ± 0.3 $\pm 3^\circ$



2 CONDITION OF DELIVERY: DBL IN 1ST. LOCKING POSITION

3.APPLIED PLUG ASSY P/N:X-1897556-X

4.APPLIED TAB.CONTACT P/N: TABLE1

5 CHECK CONVERSION KEY CODE

①	①	3	GRAY	PB-GF30	0-1897555-3	LEVER HSG	1	1
		2	YELLOW	PBT	0-1897554-5	DBL HSG	1	1
②	②	1	BLACK	PBT	1-1897553-2	CAP HSG	-	1
		1	NATURAL	PBT	0-1897553-1	CAP HSG	1	-
		NO	COLOR	MATERIAL	P/N	DESCRIPTION	Q'TY	

 SHAPE OF CONVERSION TYPE	
0-1897552-1 (WHITE)	1-1897552-2 (BLACK)
	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JM JEON	 TE Connectivity			
		CHK JW JUNG				
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED	APVD HG CHO	NAME			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC -	.090 32PIN CAP ASSY(LIF)			
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT -	A2	00779	C=1897552	-
-	SEE TABLE -	CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1
						REV B1