




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECN-21-129868	23NOV2021	DRK	NRS
	B3	REVICED PER ECR-21-124520	06JAN2022	NS	CB
	B4	REVISED PER ECR-22-132933	18MAR2022	FC	CB

- NOTES:
1. FINISH: PLATE 0.000100-0.000200 THK TIN IN LOCALIZED TIN PLATE AREA, ALL OVER 0.000040-0.000080 THK NICKEL.
 2. CONTACT WILL BE LUBED WITH LUBRICANT PER TE CONNECTIVITY P/N 22014-4.
 3. WIRE RANGE: 20-18 AWG WITH ISLUATION DIAMETERS OF 0.050-0.107 INCHES.
 4. PLATE 0.000030 MIN THK SELECT GOLD IN LOCALIZEDPLATE AREA. TIP PLATING AREA PLATE TO 0.000015 MIN THK.

1	1924463-3
1 4	1924463-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DL DRUMMOND 27AUG2007	TE Connectivity			
DIMENSIONS: Inch		CHK MP TRULL 27AUG2007				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MP TRULL 27AUG2007	NAME PIN CONTACT			
0 PLC ± 1 PLC ± 2 PLC ±.02 3 PLC ±.005 4 PLC ± ANGLES ±		PRODUCT SPEC -	SIZE A2			
MATERIAL 0.014THK CU ALLOY		APPLICATION SPEC -	CAGE CODE 100779			
		WEIGHT -	DRAWING NO 1924463			
		CUSTOMER DRAWING	SCALE 10:1		SHEET 1 OF 1	REV B4