


4




3

8 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIAMATE AREA.



I.4 — REF



	2					1		
LOC	DIST				REVISIONS			
АD	00	Р	LTR		DESCRIPTION	DATE	DWN	APVD
			D	REVISED PER	ECO-13-002771	22FEB201	3 KH	RP
			E	REVISED PER	ECO-19-009248	03JUL201	9 A P	SY

SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIAMATE AREA. MATERIAL: CONTACT AND SHIELD - PHOS BRONZE HOUSING AND CHICKLET - LCP, UL 94V-0, COLOR - BLACK

CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).

COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL. SHIELD I.27µm MIN NICKEL.

2 CONNECTOR MARKED ON EITHER SIDE OF HOUSING WITH PART NUMBER, DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN.

 $\boxed{3}$ dimension applies to centerline of thru hole.

4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE I, NOVEMBER 1995.

5 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.

27 The grounds in each column are commoned.

21JUL200 **STE** TE Connectivity 2 | JUL 2007 <u>. davis</u> TOLERANCES UNLESS OTHERWISE SPECIFIED: 24JAN2008 RECEPTACLE ASSEMBLY, 5 PAIR, IO COLUMN <u>R.PATTERSC</u> roduct spec PPLICATION SPEC IZE CAGE CODE DRAWING NO RESTRICTED 100779 C= 1934220 2scale 6:1 sheet of rev F STOMER DRAWING

| 934220-

PART NUMBER