




LOC		DIST		REVISONS				
GP	00	P	LTR	DESCRIPTION		DATE	DWN	APVD
		D		REVISED PER ECO-13-002771		26FEB2013	KH	RP





- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.

6 $\varnothing 0.05$ X Y
FINISHED HOLE SIZE
AND PLATED THRU HOLES



○ = SIGNAL
◻ = GROUND
RECOMMENDED PC BOARD LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 5:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. MAGARO 05MAY2008	 TE Connectivity			
DIMENSIONS:		CHK W. DAVIS 05MAY2008				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. DAVIS 05MAY2008	NAME			
		PRODUCT SPEC	HEADER ASSEMBLY, OPEN ENDED, 6 PAIR 16 COLUMN TinMan			
	ANGLES	APPLICATION SPEC	SIZE			
		FINISH	A100779C=1934516			
CUSTOMER DRAWING		WEIGHT	RESTRICTED TO			
				SCALE 6:1	SHEET 1 OF 1	REV D