




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		B		REVISED PER ECO-13-002771	20MAR2013	KH
		C		REVISED PER ECO-19-009248	09JUL2019	AP

D

C

B

A





SECTION W-W

C

B

A



○ = SIGNAL
⊗ = GROUND

RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303-1; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE). COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, 85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA.

1934978-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.K.SHOBER 01JUN2009	TE Connectivity	
DIMENSIONS:		CHK C.RITIER 01JUN2009		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	NAME	
0 PLC ±°	1 PLC ±°	PRODUCT SPEC	HEADER ASSEMBLY, DOUBLE ENDED 3 PAIR, 16 COLUMN TinMan 85 OHM	
2 PLC ±°	3 PLC ±°	108-2303-1		
4 PLC ±°	ANGLES ±°	APPLICATION SPEC	SIZE	
114-13243	FINISH	114-13243	CAGE CODE DRAWING NO	
MATERIAL	1	2	A100779C=1934978	
CUSTOMER DRAWING		WEIGHT	RESTRICTED TO	
			SCALE 5:1 SHEET 1 OF 1 REV C	