


1. MAXIMUM CONNECTOR INSERTION LOSS: 0.5 dB MPX
0.5 dB LC
- 2 SEE TRACE LABEL DETAIL.
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TE CONNECTIVITY SPEC TEC-138-702.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		4	PRELIMINARY, REVISE MPX B TO LC FIBER PATH	15MAY12	KG	DK



MPX FIBER POSITION		LC DUPLEX CONN	
MPX	FIBER	LC PAIR	LC FIBER
B	1	12	A
	2	11	A
	3	10	A
	4	9	A
	5	8	A
	6	7	A
	7	6	A
	8	5	A
	9	4	A
	10	3	A
	11	2	A
	12	1	A
A	1	1	B
	2	2	B
	3	3	B
	4	4	B
	5	5	B
	6	6	B
	7	7	B
	8	8	B
	9	9	B
	10	10	B
	11	11	B
	12	12	B

TEC LOGO - 


XXXXXXXXXXXXXXXXX - TRACE NO.
1938466-X - TE CONNECTIVITY P/N

2 TRACE LABEL DETAIL
(NOT TO SCALE)

DESIGN APPROVED THIS PRINT IS

PRELIMINARY

TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.GLATFELTER 28JAN2010	 TE Connectivity			
DIMENSIONS: INCHES		CHK J.BARRY 28JAN2010				
		APVD J.BARRY 28JAN2010	NAME CABLE ASSEMBLY, FIBER OPTIC 24 FIBER 50/125um, (2) LIGHTRAY MPX W/PINS TO (12) LC DUPLEX			
		PRODUCT SPEC - APPLICATION SPEC -	SIZE A2			
MATERIAL -		FINISH -	WEIGHT -		CAGE CODE 00779	
			DRAWING NO 1938466		RESTRICTED TO -	
			CUSTOMER DRAWING		SCALE NTS	SHEET 1 of 1
					REV 4	

LIGHTRAY MPX FIBER ROUTING