


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	29AUG2023	ASB	JSB
	L1	DRAWING RE-CREATED IN CREO	30NOV2023	ASB	JDB
	L2	REEL CORE DIA CHANGE	23JUL2024	SS	LET





INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED





INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY
③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3




TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS



CONSIDER MOUNTING POSITION; PEG RIGHT




PCB-LAYOUT PROPOSAL



3D VIEW
SCALE 2:1

1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3-16-DOC-1806-00915
2. COPLANARITY OF ALL CLIPS ≤ 0,1MM
- ③ PART: 100 PCS. IN BUBBLE BAGS / BULK

1	1	-	-	TAPE & REEL	6
1	-	-	-	PAD	5
1	1	1	-	SOLDER CLIP LEFT	4
1	1	1	-	SOLDER CLIP RIGHT	3
5	5	5	-	PINS	2
1	1	1	-	HOUSING	1
454950-E	224064-E	194781-E	REV	DESCRIPTION	ITEM NO.
-	-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY			PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S ADRUSH 16AUG2023	 TE Connectivity					
DIMENSIONS: mm		CHK M SZELAG 18AUG2023						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mk ISO 8015	APVD J DE BRUIJN 18AUG2023	NAME M12 FEMALE, A CODE, 5P, 17MM SMT					
		PRODUCT SPEC 108-94887						
		APPLICATION SPEC 114-94781	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		MATERIAL	FINISH	WEIGHT	A2		00779	C=194781-E
CUSTOMER DRAWING			SCALE	5:1	SHEET	1 of 1	REV	L2