



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

|   |           |
|---|-----------|
| INSERT & FUNNEL: BRASS ASTM B36<br>NICKEL PL QQ-N-290 .000300 AVG THK     | 1958054-1 |
| BODY: COPPER ASTM-B187 ANNEALED<br>NICKEL PL .000300 MIN THK PER QQ-N-290 |           |
| MATERIAL & FINISH   | PART NO.  |

|   |  |  |  |   |           |            |               |     |   |
|---|--|--|--|---|-----------|------------|---------------|-----|---|
| THIS DRAWING IS A CONTROLLED DOCUMENT.  |  | DWN<br>jr ruth<br>08JAN07                  |  |  TE Connectivity |           |            |               |     |   |
|   |  | CHK<br>JOHN KNOLL<br>08JAN07               |  |   |           |            |               |     |   |
| DIMENSIONS:<br>INCHES   |  | TOLERANCES, UNLESS<br>OTHERWISE SPECIFIED: |  | NAME  |           |            |               |     |   |
|  |  | APVD<br>JOHN KNOLL<br>08JAN07              |  | WIRE TERMINAL, RING TONGUE,<br>SEALED COPALUM, HIGH TEMP,<br>WIRE SIZE: 4/0 AL                        |           |            |               |     |   |
|   |  | PRODUCT SPEC                               |  |   |           |            |               |     |   |
|   |  | APPLICATION SPEC                           |  |   |           |            |               |     |   |
|   |  | —  |  |   |           |            |               |     |   |
| MATERIAL  |  | FINISH                                     |  | SIZE  | CAGE CODE | DRAWING NO | RESTRICTED TO |     |   |
| SEE TABLE   |  | SEE TABLE                                  |  | WEIGHT<br>100 GRAMS   | A2 00779  | C=1958054  | —             |     |   |
| CUSTOMER DRAWING  |  |  |  | SCALE   | 2:1       | SHEET      | 1 of 1        | REV | D |