





- 1 WIRE INSULATION: 10.79–11.94 [.425–.470] DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 FLASH PERMITTED ±.020

BODY: COPPER ASTM-B187 ANNEALED TIN PL PER ASTM B-545 .000150 MIN THK INSERT & FUNNEL: BRASS PER ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	1958195-1
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 12MAR08		 TE Connectivity	
		CHK RAY LONDON 12MAR08			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, RING TONGUE, SEALED COPALUM, WIRE SIZE: 1/0 AL – 2 CU	
	0 PLC ± –		APVD RAY LONDON 12MAR08		
	1 PLC ± –		PRODUCT SPEC		
	2 PLC ± 0.51[.020]		—		
	3 PLC ± –		APPLICATION SPEC		
		4 PLC ± –			
MATERIAL		FINISH		SIZE	
SEE TABLE		SEE TABLE		CAGE CODE	
		WEIGHT —		DRAWING NO	
		CUSTOMER DRAWING		RESTRICTED TO	
				A2 00779 C=1958195 —	
				SCALE 2:1 SHEET 1 of 1 REV B	