


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - C

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		E	REVISED PER ECO-16-009651	29JUL2016	RS	CT



- 1 WIRE INSULATION: .520—.633 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 STAMP "AMP 3/0 AL N" SIZE AND LOCATION APPROX AS SHOWN



INSERT & FUNNEL: BRASS MIL-C-50 NICKEL PL .000100 MIN THK PER QQ-N-290	1958091-1
BODY: COPPER ASTM-B187 ANNEALED NICKEL PL .000300 MIN THK PER QQ-N-290	
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 23FEB07		 TE Connectivity					
		CHK J KNOLL 23FEB07							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
		APVD J KNOLL 23FEB07		WIRE TERMINAL, RING TONGUE, SEALED COPALUM, HIGH TEMP, WIRE SIZE: 3/0 ALUMINUM					
		PRODUCT SPEC —							
		APPLICATION SPEC —							
		—							
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
SEE TABLE		SEE TABLE		WEIGHT 103 ± 5 g	A2 00779	C=1958091	—		
CUSTOMER DRAWING				SCALE	2:1	SHEET	1 of 1	REV	E