


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REVISED PER ECO-15-017991	06JAN16	KG	PD



- 1 WIRE INSULATION: .520—.633 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 STAMP "AMP 3/0 AL N" SIZE AND LOCATION APPROX AS SHOWN



INSERT & FUNNEL: BRASS MIL-C-50 NICKEL PL .000100 MIN THK PER QQ-N-290	1958231-1
BODY: COPPER ASTM-B187 ANNEALED NICKEL PL .000300 MIN THK PER QQ-N-290	
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 11JUN08		 TE Connectivity	
DIMENSIONS: INCHES		CHK RAY LONDON 11JUN08			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RAY LONDON 11JUN08		NAME WIRE TERMINAL, RING TONGUE, 2 HOLE, SEALED COPALUM, HIGH TEMP, WIRE SIZE: 3/0 ALUMINUM
			PRODUCT SPEC		
	0 PLC ± -		—		
	1 PLC ± -		APPLICATION SPEC		
	2 PLC ± -		—		
	3 PLC ± -				SIZE CAGE CODE DRAWING NO RESTRICTED TO
	4 PLC ± -.008				
	ANGLES ± -		—		
MATERIAL SEE TABLE	FINISH SEE TABLE		WEIGHT 128±5 GRAMS		A2 00779 C=1958231
CUSTOMER DRAWING			SCALE 2:1		SHEET 1 of 1
			REV D		