





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECO-10-001873	19FEB2010	DH	JE
	A2	REVISED PER ECO-15-004981	31MAR2015	RG	MC



SCALE 4.000



- NOTES:
- UNLESS OTHERWISE SPECIFIED
- INTERPRET DRAWING PER ASME Y14.5M - 1994.
 - 0.2mm MAX BURR.
 - VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
 - RoHS COMPLIANT AND CERTIFIED.

BALCK ANODIZED	ALUMINUM	1963843-5
NICKEL PLATED	ALUMINUM	1963843-3
NONE	ALUMINUM	1963843-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. TAO 6-17-08	TE Connectivity OSFP SINGLE LAN EXTRUSION HEATSINK 13.5mm TALL	
DIMENSIONS:		CHK B. PETROCELLI 6-23-08		
mm		APVD -		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC -		
0 PLC $\pm .2$		APPLICATION SPEC -	SIZE A100779	CAGE CODE C=1963843
1 PLC ± 0.2		WEIGHT -		
2 PLC ± 0.10		CUSTOMER DRAWING	SCALE 6.000	SHEET 1
3 PLC ± 0.08			OF 1	REV A2
4 PLC $\pm .4^\circ$				
ANGLES $\pm 4^\circ$				
FINISH -				
MATERIAL TBD SEE TABLE				
SEE TABLE				