



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
CE	16		C	ECR-14-011637	14AUG2014	HZ

- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 1.5dB/km AT 1300nm. (MEASURED AGAINST A REFERENCE LEAD)
2. TEST DATA PROVIDED WITH EACH ASSEMBLY.
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE STANDARD TEC-138-702.



FIBER PATH
DETAIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.W.DAVIS 30OCT07	 TE Connectivity			
		CHK J.DUNCAN 30OCT07				
DIMENSIONS: METERS [INCHES]		APVD D.BAECHTLE 30OCT07	NAME CABLE ASSEMBLY, FIBER OPTIC, 50/125, 2 FIBER BREAKOUT, SEALED LC DUPLEX (ODVA), BOTH ENDS			
		PRODUCT SPEC —				
		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1985363	RESTRICTED TO —
MATERIAL —	FINISH —	WEIGHT —				
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 2	REV C	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

0.95	300.00±3.00 [11811±118]	8-1985363-2
0.72	150.00±1.50 [5906±59]	8-1985363-1
0.65	100.00±1.00 [3937±39]	8-1985363-0
0.58	50.00±0.50 [1969±20]	5-1985363-0
0.56	40.00±0.40 [1575±16]	4-1985363-0
0.56	39.00±0.39 [1535±15]	3-1985363-9
0.56	38.00±0.38 [1496±15]	3-1985363-8
0.56	37.00±0.37 [1457±15]	3-1985363-7
0.55	36.00±0.36 [1417±14]	3-1985363-6
0.55	35.00±0.35 [1378±14]	3-1985363-5
0.55	34.00±0.34 [1339±13]	3-1985363-4
0.55	33.00±0.33 [1299±13]	3-1985363-3
0.55	32.00±0.32 [1260±13]	3-1985363-2
0.55	31.00±0.30 [1220±12]	3-1985363-1
0.54	30.00±0.30 [1181±12]	3-1985363-0
0.54	29.00±0.30 [1141.7±12.0]	2-1985363-9
0.54	28.00±0.30 [1102.4±12.0]	2-1985363-8
0.54	27.00±0.30 [1063.0±12.0]	2-1985363-7
0.54	26.00±0.30 [1023.6±12.0]	2-1985363-6
0.54	25.00±0.30 [984.2±12.0]	2-1985363-5
0.54	24.00±0.30 [944.9±12.0]	2-1985363-4
0.53	23.00±0.30 [905.5±12.0]	2-1985363-3
0.53	22.00±0.30 [866.1±12.0]	2-1985363-2
0.53	21.00±0.30 [826.8±12.0]	2-1985363-1
0.53	20.00±0.30 [787.4±12.0]	2-1985363-0
0.53	19.00±0.30 [748.0±12.0]	1-1985363-9
0.53	18.00±0.30 [708.7±12.0]	1-1985363-8
0.53	17.00±0.30 [669.3±12.0]	1-1985363-7
0.52	16.00±0.30 [629.9±12.0]	1-1985363-6
0.52	15.00±0.30 [590.6±12.0]	1-1985363-5
0.52	14.00±0.15 [551.2±6.0]	1-1985363-4
0.52	13.00±0.15 [511.8±6.0]	1-1985363-3
0.52	12.00±0.15 [472.4±6.0]	1-1985363-2
0.52	11.00±0.15 [433.1±6.0]	1-1985363-1
0.52	10.00±0.15 [393.7±6.0]	1-1985363-0
0.51	9.00±0.15 [354.3±6.0]	1985363-9
0.51	8.00±0.08 [315.0±3.0]	1985363-8
0.51	7.00±0.08 [275.6±3.0]	1985363-7
0.51	6.00±0.08 [236.2±3.0]	1985363-6
0.51	5.00±0.08 [196.8±3.0]	1985363-5
0.51	4.00±0.05 [118.1±2.0]	1985363-4
0.50	3.00±0.05 [118.1±2.0]	1985363-3
0.50	2.00±0.05 [78.7±2.0]	1985363-2
0.50	1.00±0.05 [39.4±2.0]	1985363-1

MAX IL (dB)	L METERS [INCHES]	PART NUMBER
----------------	-------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.W.DAVIS 300CT07 CHK J.DUNCAN 300CT07 APVD D.BAFCHTLE 300CT07		 TE Connectivity				
DIMENSIONS: METERS [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSEMBLY, FIBER OPTIC, 50/125, 2 FIBER BREAKOUT, SEALED LC DUPLEX (ODVA), BOTH ENDS				
		PRODUCT SPEC —						
		APPLICATION SPEC —						
MATERIAL —		FINISH — WEIGHT —		SIZE A2	GAGE CODE 00779	DRAWING NO C-1985363	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS	SHEET 2 of 2	REV C