




$\varnothing 3.18 \pm 0.13$
 $[\varnothing 1.125 \pm .005]$
 $\oplus \varnothing 0.15 \text{ [.006]} \text{ (M)}$



RECOMMENDED LAYOUT

1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.

2 CONTACT MATERIAL: PHOSPHOR BRONZE.

3 0.76um [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

	YES	1986647-1
CONTACT FINISH	MOUNTING TABS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 30APR10		 TE Connectivity	
		CHK STEVE HEADER 30APR10			
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD STEVE HEADER 30APR10 PRODUCT SPEC 108-10033 APPLICATION SPEC -	
		MATERIAL 		NAME SOCKET HEADER ASSEMBLY, 9 POSITION, METRIMATE	
FINISH -		WEIGHT -		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-1986647	RESTRICTED TO -
				SCALE 4:1	SHEET 1 of 1
				REV C	