


4

3


2

1



LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			1	—	3/19/08	SS	CR



CLAMPING SCREW



WIRE ENTRY



MATING FACE


MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: BLACK.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M2, BRASS, NICKEL PLATED.

ELECTRICAL:
VOLTAGE RATING: 300V
CURRENT RATING: 11A
WIRE SIZE RANGE: 14-30 AWG

ENVIRONMENTAL:
OPERATING TEMP RANGE: -40°C TO +110°C

THIS PRINT IS
PRELIMINARY
PRIOR TO CUSTOMER ORDER
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

56.0	16	1-1986367-6
52.5	15	1-1986367-5
49.0	14	1-1986367-4
45.5	13	1-1986367-3
42.0	12	1-1986367-2
38.5	11	1-1986367-1
35.0	10	1-1986367-0
31.5	9	1986367-9
28.0	8	1986367-8
24.5	7	1986367-7
21.0	6	1986367-6
17.5	5	1986367-5
14.0	4	1986367-4
10.5	3	1986367-3
7.0	2	1986367-2
DIM L	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 18MAR2008	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK C RICHARD 3/19/08				
		APVD C RICHARD 3/19/08	NAME TERMINAL BLOCK, PLUG, VERTICAL STACKING LEFT HAND, 3.50mm PITCH			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL —		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986367	RESTRICTED TO —
		FINISH —	CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
					REV 1	