





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	A		FIRST ISSUE	26MAR2007	JM	BB
		B		ECR 07-019499	16AUG2007	JM	BB



NOTE:

- 1 Mating Part :1438188-1
- 2 'Customer part no.: 8X2T-14A594-BA'.
- 3 Performance test per USCAR 2.
 - section: 5.1.3 Material characteristics
 - 5.1.4 Temperature classification
 - 5.1.8 Visual inspection
 - 5.4.2 Connector - connector mating/unmating forces
 - 5.4.4 Polarisation effectiveness
(Incorrect mating only, not coding polarisation)
 - 5.4.5 Miscellaneous Component engage/disengage force
 - 5.4.7 Connector audible click
 - 5.4.8 Connector drop test
 - 5.6.3 High temperature exposure
 - 5.6.4 Fluid resistance
 - 5.6.6 Pressure vacuum leak
 - 5.7.2 Connector mounting feature mechanical strength
 - 5.8.1 High Pressure Spray

$\triangle 4$ 10.8 dim is measured at root. 0.4min gap allowable due to mold distortion

1991012-1
PART NO.

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN J.MARSH 26.3.07 CHK B.BAKER 26.3.07 APVD B.BAKER 26.3.07		Tyco Electronics Stanmore. UK	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.5 2 PLC ± 0.5 3 PLC \pm 4 PLC \pm ANGLES \pm		NAME KVM Blanking Plug	
MATERIAL PA66-GF30 FINISH BLACK		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A3 CAGE CODE 00779 DRAWING NO C=1991012 RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 1 REV B