


4		3		2		1															
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		- . - .		LOC		DIST		REVISIONS											
© COPYRIGHT		BY TYCO ELECTRONICS CORPORATION.		ALL RIGHTS RESERVED.		—		—		P		LTR		DESCRIPTION		DATE		DWN		APVD	
												A		RELEASED PER ECO 10-023439		11-18-10		CT		DW	
WASHER WEDGE FERRULE		BRASS PER ASTM-B-16, HALF HARD		GOLD PLATE PER ASTM-B-488																	
HOUSING COUPLING NUT CLAMP NUT		STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303		PASSIVATE PER QQ-P-35																	
DIELECTRIC		PTFE FLUOROCARBON PER ASTM-D-1457		N/A																	
CENTER CONTACT		BERYLLIUM COPPER PER ASTM-B-196 ALLOY 173		GOLD PLATE PER ASTM-B-488																	
RETAINING RING		BERYLLIUM COPPER ASTM-B-194		N/A																	
GASKET		SILICONE RUBBER PER ZZ-R-765		N/A																	
COMPONENT		MATERIAL		FINISH																	

785 MAY



ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348, Fig. 310.1	TEMPERATURE RATING -65°C TO +165°C
Frequency Range (GHz) DC to max operating frequency of cable per MIL-C-17	Recommended Mating Torque 7 to 10 inch-pounds	Vibration MIL-STD-202, Method 204, Condition D
Volt Rating (VRMS MAX) @ Sea Level 250	Mating Characteristics:	Shock MIL-STD-202, Method 213, Condition I
VSWR 1.15 +0.02 (F)GHz	Insertion (MAX Lbs) N/A	Thermal Shock MIL-STD-202, Method 107, Condition B,
Insertion Loss (dB MAX) .06 √FGHz test at f = 6.0 GHz	Withdrawal (MIN Oz) N/A	EXCEPT HIGH TEMP SHALL BE +85°C
RF Leakage (dB MIN) -60dB MIN between 2 & 3 GHz	Force to Engage and Disengage (In/Lbs MAX) 2.0	HIGH TEMP SHALL BE +200°C FOR CONNECTORS USING +200°C CABLES
Corona, 70,000 Ft (VRMS MIN) 190	Center Contact Captivation	Moisture Resistance MIL-STD-202, Method 106
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Axial (Lbs) 6 LBS MIN	Corrosion - MIL-STD-202, Method 101, Condition B
Contact Resistance (Milliohms MAX)	Radial (In/Oz) N/A	
Center Contact 3.0	Cable Retention	
Outer Contact 2.0	Axial Force (Lbs) 20	
Cable to Housing .05	Torque (In/Oz) N/A	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500	Weight (Grams) 4.8	
I.R.(Megohms MIN) 5000		

DESIGNED FOR USE WITH RG188/U CABLE	
CABLE ENTRY DIAMETER MINIMUM	
CLAMP NUT	.113 [2.87]
FERRULE	.066 [1.68]
CONTACT	.023 [0.58]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11-18-10	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES [mm]		CHK D.WILSON 11-18-10			
		APVD D.WILSON 11-18-10	NAME		
		PRODUCT SPEC	SMA STRAIGHT CABLE PLUG KIT, CLAMP ATTACHMENT		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
0 PLC ± -		—	A2	00779	C=1996173
1 PLC ± -		WEIGHT	—	—	—
2 PLC ± -		CUSTOMER DRAWING	SCALE	SHEET	REV
3 PLC ± -			8:1	1 of 1	A
4 PLC ± -					
ANGLES ± -					
FINISH					
SEE TABLE					
SEE TABLE					