



D

C


B

A



- CONNECTOR DIMENSIONS ARE PER ARINC 600 SPECIFICATION.
- CONNECTOR IS SUPPLIED WITH CONTACTS AS LISTED IN TABLE AND PACKAGED IN A SEPARATE CONTAINER.
- KEYING SHOWN IN POSITION "01" FOR ILLUSTRATION ONLY. CONNECTORS SHIPPED WITH KEYING INSTALLED IN POSITION PER TABLE. FOR POSITION "00" KEYING HARDWARE SHIPPED UNASSEMBLED.
- DUST COVER IS INCLUDED AND INSTALLED FOR SHIPPING (NOT SHOWN).

COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85	CHROMATE CONVERSION PER MIL-C-5541, TYPE II, CLASS 3
INSERT RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	CHROMATE CONVERSION PER MIL-C-5541, TYPE II, CLASS 3
SCREWS	STEEL OR STAINLESS STEEL	STAINLESS STEEL OR PASSIVATED
POLARIZING KEYS	ZINC ALLOY PER ASTM-B-86	—
POLARIZING KEY RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625
INSERTS	THERMOSET OR THERMOPLASTIC PPS PER MIL-M-24519	—

"50"	MODULE A 208264-2 (SIZE 22 CRIMP SOCKET CONTACT; QTY=150)		1996880-1		
	MODULE B NONE				
	MODULE C 208265-3 (SIZE 20 CRIMP PIN CONTACT; QTY=4) 208268-3 (SIZE 16 CRIMP PIN CONTACT; QTY=3) 208271-3 (SIZE 12 CRIMP PIN CONTACT; QTY=4) 225790-5 (SIZE 5 CRIMP PIN CONTACT; QTY=2) FOR RG/U 174, 188 OR 316 CABLE				
KEYING POSITION	CONTACTS INCLUDED AND NOT INSTALLED		PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 7-25-08 CHK K.THACKSTON 7-25-08 APVD K.THACKSTON 7-25-08	 TE Connectivity Ltd. RCPT ASSY,SIZE 2,ARINC 600 (150/DUMMY/13C2), RR —		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME			
	0 PLC ± —	PRODUCT SPEC			
	1 PLC ± —	—			
	2 PLC ± —	APPLICATION SPEC			
	3 PLC ± —	—			
4 PLC ± —	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A1 00779 C-1996880		—
SEE TABLE	SEE TABLE	CUSTOMER DRAWING	SCALE 3:2	SHEET 1 OF 1	REV D