CATALOG # 1EEAP SAFETY ORGANIZATIONS RELIABILITY SPECIFICATIONS: ECN # APPRVD. DATE STORAGE TEMPERATURE: -40°C TO +85°C ECO-09-026495 10DEC09 THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED HUMIDITY: 21 DAYS @ 40°C 95% RH. BY THE LISTED AGENCY, THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED CURRENT OVERLOAD TEST: 6 TIMES I_r FOR 8 SECONDS IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET: TEST SPECIFICATIONS: UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA 22.2, # 8 INDUCTANCE: 10.0 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C) VDE APPROVED: VDE 565-3 LINE TO GROUND: 0.0053 μF ±20% OPERATING SPECIFICATIONS 0.0105 μF ±20% LINE TO LINE: DISCHARGE RESISTOR: 1.5 MA LINE CURRENT/VOLTAGE: 1 AMP, 120/250 VAC, L/G AND L/L I.R 1 AMP/40°C, 250 VAC NO DISCHARGE RESISTOR: 6000M₁ (MIN.) @ 100VDC, 20°C AND 50% RH LINE FREQUENCY: 50-60Hz MAXIMUM LEAKAGE CURRENT, RECOMMENDED RECEIVING INSPECTION HIPOT: EACH LINE TO GROUND: 0.22 mA@ 120V 60Hz LINE TO GROUND: 1500VAC OR 2250VDC FOR 1 MINUTE 0.38 mA@ 250V 50Hz LINE TO LINE: 1450VDC FOR 1 MINUTE OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ir. FILTER APPROVAL: IN AN AMBIENT, To, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, Io, IS AS FOLLOWS: T = T - $\sqrt{85-$ T $^{\circ}$ THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR $I_0 = I_r -$ YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT. - 1.98 MAX.-1.54 MAX. — 0.81 MAX. 1.575±.015 - \mathbb{I} 0.138 ±.010 0.537 ±.020 0.380 MAX. 0.560 Ø 0.132±.01 WITH ±.015 Ø 0.260 REF X 90° 0.031 SQ.±.003-0.551 COUNTERSUNK HOLE FOR (3 PINS) ±.010 #4 FLAT HEAD SCREW (2X) R = 0.234 (4X) - \emptyset 0.140 (2X) \neg \emptyset 0.075 -(3 HOLES) 0.900 1.13 0 MAX. - 1.200 - 1.575 -0.520 PANEL CUTOUT (BACK MOUNT) 0.551 TOLERANCE ±.005 - 0.685±.015 (CENTER PIN TO PANEL) PC LAYDUT 1609000-3 OBSOLETE 6609000-3 1) obsolete parts: obsolete cis streamlining per d.renaud/d.sinisi 50 (MINIMUM) INSERTION THIRD ANGLE 50<u>~</u>-LDSSPROJECTION FREQUENCY 844 E. ROCKLAND RD. LIBERTYVILLE IL 60048 1.5 5 30 01 . 05 | . 10 . 15 . 50 10 UNLESS OTHERWISE SPECIFIED. MHz TOLERANCE TO BE ±.025 POWER LINE FILTER COMMON MATERIAL & FINISH: AS SUPPLIED 41 12 23 29 32 47 47 47 40 This document is proprietary to CORCOM INC. CAD FILE: C:NCKNCDNIEEAPOO dΒ DATE: 3/24/97 CATALOG NO. REV. and is not to be reproduced nor used for ZTM DIFF. 9 19 42 45 45 nanufacturing purposes except on CORCOM'S 1EEAP 1 DRW. BY: ORIG: dΒ

prior written consent.

KAW