




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-22-147358	05APR2022	KR	RM
	A2	REVISED PER ECR-25-242230	29APR2025	GH	CS




TEPN	DESCRIPTION	RAL NUMBER	COLOR	THREAD TYPE	TL	H	ØD MAX	SW 1
1SNG611001R0000	EP-DRP-M12-LGR-A	7035	L.GREY	M12x1.5	12.0	17.0	19.0	17
1SNG611002R0000	EP-DRP-M12-GR-A	7001	GREY	M12x1.5	12.0	17.0	19.0	17
1SNG611003R0000	EP-DRP-M12-BL-A	9005	BLACK	M12x1.5	12.0	17.0	19.0	17



- INGRESS PROTECTION RATING : IP56 - IP 66 (CATEGORY 2)
- OPERATING TEMPERATURE : -20°C TO 100°C
- WATER FLOW RATE : 30 $\pm$ 5 ML / MIN. AT Δ P = 1 MBAR
- AIR FLOW RATE Δ P=70 MBAR : 3.5 LT/MIN. (210 LT/H)

1	PA 66 V2	RING	4
1	PA 66 V2	CAP	3
1	PA 66 V2	WATER DEVIATOR	2
1	PA 66 V2	BODY	1
QTY	MATERIAL	DESCRIPTION	ITEM NO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17MAR2022 Rajan n. Kasi	 TE Connectivity			
DIMENSIONS: mm		CHK 17MAR2022 Rafeeq. Mohd				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 17MAR2022 Rafeeq. Mohd	NAME - M-DRAIN-PLUG-PA			
0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ - 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ -		PRODUCT SPEC -	SIZE A3			
MATERIAL REF, TABLE -		APPLICATION SPEC -	CAGE CODE 00779			
		WEIGHT -	DRAWING NO C-1SNP061330-0100			
		CUSTOMER DRAWING	SCALE 2:1		SHEET 1 OF 1	REV A2