SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA 22.2, # 8 VDE APPROVED: EN 133200

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 1 AMP/40°C, 120/250VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND: 0.22mA @ 120V, 60Hz 0.38mA @ 250V, 50Hz

OPERATING AMBIENT TEMP. RANGE: -10° C TO $+40^{\circ}$ C @ RATED CURRENT, I_C.

IN AN AMBIENT, T_0 , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_0 = I_0 - \sqrt{100 - I_0}$

 $I_0 = I_r - \sqrt{\frac{100 - T_0}{20}}$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES Ir FOR 8 SECONDS

TEST SPECIFICATIONS:

INDUCTANCE: 10.0mH NOMINAL

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

0.0053µF ±20% LINE TO GROUND: LINE TO LINE: 0.101µF ±20% DISCHARGE RESISTOR: 1.5M 介

L/G AND L/L I.R

NO DISCHARGE RESISTOR: 6000M₁ (MIN.) @ 100VDC,

20°C AND 50% RH

CATALOG # 1EGS1-1

ECO # APPRVO. DATE

17JUL07


RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500VAC OR 2250VDC FOR 1 MINUTE

LINE TO LINE: 1450VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



	50A- 50A(MINIMUM) INSERTION LOSS											
	FREQUENCY MHz	0.01	0.05	0.10	0.15	0.5	1.0	3.0	5.0	10	30	
	COMMON dB	12	23	29	32	41	47	-	50	50	55	
	DIFF. dB	1	-	-	3	14	23	41	47	50	44	

PROJECTION	\bigcirc		
UNLESS OTHE	RWISE SI	PECIF:	IED,
TOLERANCE T	[O BE ±.0	025	
MATERIAL &	FINISH:	IZ ZA	JPPL I E D

THIRD ANGLE

This document is proprietary to CORCOM INC and is not to be reproduced nor used for nanufacturing purposes except on CORCOM'S prior written consent.



CUSTOMER DRAWING 1EGS1-1

00010			
	5609117-1		
SCALE: NTS	DATE: 140CT03	CATALOG NO.	REV.
DRW. BY: JF	DRIG: KAW	1EGS1-1	l RI