



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	25FEB2022	PS	RM


SECTION A-A



TCPN	TE Product Type (Entrelec)	PG DIN 40430	H	TL	X	O-RING $\varnothing$
1SNG621009R0000	EM-ROP-PG7-MET-A	PG 7	3.0	6.0	16.0	9.5x1.5
1SNG621010R0000	EM-ROP-PG9-MET-A	PG 9	3.0	6.0	19.0	12.0x1.5
1SNG621011R0000	EM-ROP-PG11-MET-A	PG 11	3.0	6.0	22.0	15.0x1.5
1SNG621012R0000	EM-ROP-PG135-MET-A	PG 13.5	3.0	6.5	24.0	16.0x1.5
1SNG621013R0000	EM-ROP-PG16-MET-A	PG 16	3.0	6.5	26.0	18.0x1.5
1SNG621014R0000	EM-ROP-PG21-MET-A	PG 21	4.0	7.0	33.0	23.0x2.0
1SNG621015R0000	EM-ROP-PG29-MET-A	PG 29	4.0	8.0	42.0	31.0x2.0
1SNG621016R0000	EM-ROP-PG36-MET-A	PG 36	6.0	9.0	52.0	40.0x2.0
1SNG621017R0000	EM-ROP-PG42-MET-A	PG 42	6.0	10.0	59.0	45.0x2.0
1SNG621018R0000	EM-ROP-PG48-MET-A	PG 48	6.0	10.0	66.0	54.0x2.6

Temperature range
With Nitrile O-ring -30°C to +100°C
With Silicone O-ring -60°C to +140°C

Protection Class IP 68

2	1	O-RING		-	NBR		-				
1	1	BLIND STOPS		-	Brass (Nickel plated)		-				
RPT	QTY	DOC TITLE		DRAWING NUMBER		MATERIAL		COMMENTS			
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 25FEB2022 Shinde, Puneet	TE Connectivity						
				CHK 25FEB2022 Rajan n. Kasi							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 25FEB2022 Rafeeq. Mohd					NAME - PG-ROUND-PLUG-METAL		
				PRODUCT SPEC PG-ROUND-PLUNG-METAL							
		0 PLC ±.1 1 PLC ±.1 2 PLC ±.1 3 PLC ±.1 4 PLC ±.1 ANGLES ±.1		APPLICATION SPEC -	SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO -		
				WEIGHT -	A 3		00779	©=1SNP061355-0100			
MATERIAL REF, TABLE -		FINISH REF, TABLE -		CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV A		