






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	14FEB2022	PS	SB
	A1	Range expansion	16MAY2023	VR	VR





SECTION A-A




SECTION B-B



axe du profile
axis of profile



hauteur hors tout sur profile
overall height on profile



1SNF526011R0000
PART NO.

CBS95-2P...

UL 1059

CSA C22.2 No. 158-10

1000 V 3/0 AWG

Cu 200 A - 22,6 Nm*

Al 155 A - 22,6 Nm*

IEC 60947-7-1

IEC 61238-1

1000 V AC/DC 95mm²

Cu 232 A - 19 Nm*

Al 200 A - 22,6 Nm*

* see instruction leaflet

C (7:2)

THIS DRAWING IS A CONTROLLED DOCUMENT.		16 May-23 10:36:07 AM Villard, Romain		TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CBS95-2P 1SNF526011R0000	
		0 PLC ± 1 PLC ±0,1 2 PLC ±0,01 3 PLC ±0,005 4 PLC ±0,0001 ANGLES ±		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL		FINISH		A 3 00779 C-1SNP300335-0100	
-		-		Customer Drawing	
-		finish_spec_2		SCALE 11:20 SHEET 1 OF 1 REV A1	