





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
HB	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D		REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	120ct2015	HYS	CSM



CONNECTION FIGURE





FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING (BOTTOM VIEW)

Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Huang.Yunshou		
DIMENSIONS: mm		CHK	Yu.Banghua		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	Zhang.Sunny		
0 PLC ± -		PRODUCT SPEC	-		
1 PLC ± -		APPLICATION SPEC	-		
2 PLC ± -		WEIGHT	-		
3 PLC ± -		STE TE Connectivity OJ-SS-LM SPEC 043 CUSTOMER DRAWING			
4 PLC ± -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
ANGLES ± -		A3	00779	②=2-1419129-2	-
FINISH		CUSTOMER DRAWING			
MATERIAL		SCALE	SHEET	REV	
		5:1	1 OF 2	D	

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.-
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
HB	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

NOTE:
 1. TERMINAL DIMENSIONS BEFORE SOLDER DIP
 2. LOT NO. SYSTEM AS FOLLOWING:




③ 3. FOR THE TIN-PLATING OF THE PINS:
 +0.1mm FOR WIDTH, THICKNESS AND DIAMETER.
 +0.5mm FOR LENGTH.

④ 4. MARKING FROM INK TO LASER.

⑤ 5. ADD LOT NO. SYSTEM AS FOLLOWING;
 I, DIGITS FOR DAY OF THE WEEK
 1...MONDAY IN THIS WEEK;
 2...TUESDAY IN THIS WEEK;

 7...SUNDAY IN THIS WEEK
 II, DIGITS FOR SHIFT OF THE DAY
 1...DAY SHIFT IN THIS DAY;
 2...NIGHT SHIFT IN THIS DAY;
 III, ONE CHARACTER DISTINGUISH THE
 LINE IDENTITY, SUCH AS: A,B,....Z



2-1419129-2	OJ-SS-112LM	107-79010	a
TE PART NO	TE TYPE NAME	PARKING SPEC	TYPE

RELAY TYPE

INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
		P.B.T	CASE	13
		P.B.T	BASE	12
		P.B.T	BOBBIN	11
		SOLDER DIP	COIL TERMINAL	10
		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
		SOLDER DIP	NO.TERMINAL	5
		Cu ALLOY	MOVABLE SPRING	4
		NIP	CORE	3
		NIP	ARMATURE	2
		NIP	YOKE	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Huang.Yunshou	
DIMENSIONS: mm		CHK	Yu.Banghua	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	Zhang.Sunny	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		CUSTOMER DRAWING		
4 PLC ± -		SIZE	A3	CAGE CODE
ANGLES ± -		DRAWING NO	G=2-1419129-2	
FINISH		RESTRICTED TO	-	
MATERIAL		SCALE	5:1	SHEET
		2 OF 2		REV
				D



OJ-SS-LM SPEC 043 CUSTOMER DRAWING