




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED AS PER ECR-24-219489	04SEP2024	GH	CS

SECTION A-A



TCPN	TE Product Type (Entrelec)	M EN 60423	TL	H	ØD	SW 1	SW 2	Clamping Range Ø min - max	Shield Diameter Ø min-max
1SNG614001R0000	EM-EMC 4-M12-MET-A	M12x1.5	6.0	28.1	15.5	14	14	3.0 - 6.5	2.0 - 5.0
1SNG614002R0000	EM-EMC 4-M16-MET-A	M16x1.5	6.0	34.5	22.0	20	20	5.0 - 10.0	3.5 - 8.0
1SNG614003R0000	EM-EMC 4-M20-MET-A	M20x1.5	6.0	31.7	24.5	22	22	6.0 - 12.0	4.5 - 10.0
1SNG614004R0000	EM-EMC 4-M20-MET-B	M20x1.5	8.0	39.7	26.8	24	24	7.5 - 14.0	5.5 - 11.5
1SNG614005R0000	EM-EMC 4-M25-MET-A	M25x1.5	8.0	43.1	33.0	30	30	10.0 - 18.0	7.0 - 14.0
1SNG614006R0000	EM-EMC 4-M32-MET-A	M32x1.5	9.0	52.9	43.5	40	40	16.0 - 25.0	12.0 - 20.0
1SNG614007R0000	EM-EMC 4-M40-MET-A	M40x1.5	9.0	60.7	55.5	50	50	22.0 - 32.0	18.0 - 27.0
1SNG614008R0000	EM-EMC 4-M50-MET-A	M50x1.5	9.0	72.0	64.0	58	58	30.0 - 38.0	26.0 - 34.0
1SNG614009R0000	EM-EMC 4-M63-MET-A	M63x1.5	14.0	58.2	75.0	64	68	34.0 - 44.0	30.0 - 40.0
1SNG614010R0000	EM-EMC 4-M63-MET-B	M63x1.5	10.0	73.1	83.0	75	75	37.0 - 53.0	33.0 - 49.0

NBR	1	O-RING	7
Brass (Nickel plated)	1	GLANDS CAP	6
CR	1	SEAL	5
PA6 V2	1	PLASTIC INSERT	4
Brass (Nickel plated)	1	EMC PRESSURE RING	3
CuBe (Tin Plated)	1	EMC SPRING	2
Brass (Nickel plated)	1	EMC CABLE GLAND BODY	1
MATERIAL	QTY	DESCRIPTION	ITEM NO.

la quantite indiquée peut correspondre a une unite particuliere: voir : Observations (par colisage, longueur...) The quantity indicated may refer to a particular unit, see remarks (package, length...)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22MAR2022 Rajan n. Kasi	 TE Connectivity	
DIMENSIONS: mm		CHK 22MAR2022 Rafeeq. Mohd		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 22MAR2022 Rafeeq. Mohd	NAME M-EMC 4-GLAND	
0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±0.5		PRODUCT SPEC M-EMC 4-GLAND	SIZE A3	
MATERIAL REF. TABLE		APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO. C=1SNP061364-0100
FINISH REF. TABLE		WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1
			REV A2	