





REVISIONS					
P.	LTR	DESCRIPTION	DATE	DWN	APVD
1		PROPOSED DESIGN	27FEB2021	CZ	SH
2		CHANGED UNIT TO MM	03APR2021	CZ	SH




- 1 "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2 MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-0
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS.
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7 PCB - 1.15 ±0.025 DRILLED HOLES PLATED WITH 0.0076 MIN Sn OVER 0.025 TO 0.076 Cu PLATING TO ACHIEVE A 1.02 ±0.76 HOLE



PROPOSAL ONLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. ZHOU 27FEB2021	4HDP		2-6450843-2
		CHK C. ZHOU 27FEB2021	DESCRIPTION		PART NUMBER
		APVD S. HAN 27FEB2021	NAME		
DIMENSIONS:		PRODUCT SPEC			
mm		108-2292			
		APPLICATION SPEC			
		114-13251			
		ANGLES			
		FINISH			
MATERIAL		WEIGHT			
		RESTRICTED CUSTOMER			
		SCALE			
		4:1			
		SHEET			
		1			
		OF			
		2			
		REV			
		1			

[illegible]

STD PRESS FIT POWER CONTACT, 3.05 TAIL LENGTH						TT	
HOLD DOWN, MULTI-BEAM						HD	
DESCRIPTION IDENTIFIER							
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN C. ZHOW	27FEB2021		
				CHK C. ZHOW	27FEB2021		
				APVD S. HAN	27FEB2021		
DIMENSIONS:						TE Connectivity	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ±.1		-			
		1 PLC ±.1		PRODUCT SPEC			
		2 PLC ±.1		108-2292			
		3 PLC ±.13		APPLICATION SPEC			
		4 PLC ±0.051		SIZE CASE CODE DRAWING NO		RESTRICTED TO	
		ANGLES ±.2*		A100779G=2-6450843-2			
MATERIAL		FINISH		WEIGHT			
- 2		- 3		-			
RESTRICTED CUSTOMER				SCALE		SHEET	
				4:1		2 OF 2	
						REV 1	