

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.


LOC
DSDIST
-

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A9	REVISED-PARTNO ADD (ECR-19-003425)	22.NOV.'14	YS	IH

NOTES;

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. CODE I DRAWING IS SHOWN.
3. DELIVERY CONDITION: CPA PRE-LOCK POSITION
4. INSTRUCTION SHEET: 408-61002
5. WIRE TOLERANCE (L)
500mm < L < 1000mm: +20mm
1000mm < L < 2000mm: +30mm
2000mm < L : +50mm


3D VIEW
SCALE 1:1

CONNECTOR WITH CLOSED CPA




3 CONNECTOR WITH OPEN CPA: DELIVERY CONDITION

8. COMPONENT TABLE
REFER TO DRAWING No. 2005339

TERMINAL (L/R)	MATERIAL	COPPER ALLOY			
FERRITE	MATERIAL	FERRITE (D40)			
CPA	MATERIAL	PBT-GF15			
	COLOR	ORANGE			
COVER	MATERIAL	PBT-GF15			
	COLOR	YELLOW			
HOUSING	MATERIAL	PBT-GF10	PBT-GF10	PBT-GF10	PBT-GF10
	COLOR	BLACK	GREEN	YELLOW	BLUE
	FEATURE				
			CODE I	CODE II	CODE III
TE PN / DESCRIPTION		2005339-1	2005339-2	2005339-3	2005339-4
GM PN		13577890	13577891	13577892	13577893

9. P/N LIST: SEE SHEET 2 of 2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YS JANG			TE Connectivity	
DIMENSIONS: mm		CHK -				
		APVD IH SONG		NAME		
		PRODUCT SPEC		AK-II SQUIB PIGTAIL FOR GMK/PACKARD M300/T300/J300/J305/J308/J309		
MATERIAL SEE TABLE		APPLICATION SPEC		SIZE		
		WEIGHT		CAGE CODE		
FINISH -		CUSTOMER DRAWING		DRAWING NO		
		SCALE		RESTRICTED TO		
		2:1		SHEET 1 OF 2		
		A3		REV A9		

BLACK (CODE I)	2005339-1	A8	4.0	4690	No. 1 (R)	FLRY-B 0.5SQ ORANGE/BLUE	2-2005371-2	J305 CAB RH	A4
					No. 2 (L)	FLRY-B 0.5SQ WHITE/BLACK			
				4670	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	2-2005371-1	J305 CAB LH	A4
					No. 2 (L)	FLRY-B 0.5SQ VIOLET/ORANGE			
BLACK (CODE I)	2005339-1	A8	4.0	5200	No. 1 (R)	FLRY-B 0.5SQ ORANGE/BLUE	1-2005371-9	J309 CAB RH	A3
					No. 2 (L)	FLRY-B 0.5SQ WHITE/BLACK			
				5420	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	1-2005371-8	J309 CAB LH	A3
					No. 2 (L)	FLRY-B 0.5SQ VIOLET/ORANGE			
				1980	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GRAY	1-2005371-7	J309 P/T RH	A3
					No. 2 (L)	FLRY-B 0.5SQ BLUE/ORANGE			
				2040	No. 1 (R)	FLRY-B 0.5SQ BROWN/BLUE	1-2005371-6	J309 P/T LH	A3
					No. 2 (L)	FLRY-B 0.5SQ ORANGE/RED			
BLACK (CODE I)	2005339-1			5095	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GRAY	1-2005371-3	T300 CAB RH	
					No. 2 (L)	FLRY-B 0.5SQ WHITE/ORANGE			
				5095	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	1-2005371-2	T300 CAB LH	
					No. 2 (L)	FLRY-B 0.5SQ VIOLET/ORANGE			
GREEN (CODE II)	2005339-2			2355	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	1-2005371-1	T300 P/T RH	
					No. 2 (L)	FLRY-B 0.5SQ WHITE/ORANGE			
				2355	No. 1 (R)	FLRY-B 0.5SQ ORANGE/WHITE	2005371-9	T300 P/T LH	
					No. 2 (L)	FLRY-B 0.5SQ GRAY/ORANGE			
BLACK (CODE I)	2005339-1			1940	No. 1 (R)	FLRY-B 0.5SQ YELLOW/ORANGE	1-2005371-5	M300 PAB (MFL)	
					No. 2 (L)	FLRY-B 0.5SQ ORANGE/WHITE			
				1920	No. 1 (R)	FLRY-B 0.5SQ YELLOW/ORANGE	1-2005371-4	M300 PAB (MFM)	
					No. 2 (L)	FLRY-B 0.5SQ ORANGE/WHITE			
				2120	No. 1 (R)	FLRY-B 0.5SQ YELLOW/ORANGE	2005371-8	M300 PAB (Chevy)	
					No. 2 (L)	FLRY-B 0.5SQ ORANGE/WHITE			
				1800	No. 1 (R)	FLRY-B 0.5SQ YELLOW/ORANGE	2005371-7	M300 PAB (Non Chevy)	
					No. 2 (L)	FLRY-B 0.5SQ ORANGE/WHITE			
				3340	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GRAY	2005371-6	M300 CAB RH	
					No. 2 (L)	FLRY-B 0.5SQ WHITE/ORANGE			
				2710	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	2005371-5	M300 CAB LH	
					No. 2 (L)	FLRY-B 0.5SQ VIOLET/ORANGE			
BLACK (CODE I)	2005339-1	A8	4.0	4560	No. 1 (R)	FLRY-B 0.5SQ ORANGE/BLUE	2005371-4	J300 CAB RH	
					No. 2 (L)	FLRY-B 0.5SQ WHITE/BLACK			
				4590	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	2005371-3	J300 CAB LH	
					No. 2 (L)	FLRY-B 0.5SQ VIOLET/ORANGE			
				1800	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GRAY	2005371-2	J300 P/T RH	
					No. 2 (L)	FLRY-B 0.5SQ BLUE/ORANGE			
				1960	No. 1 (R)	FLRY-B 0.5SQ BROWN/BLUE	2005371-1	J300 P/T LH	
					No. 2 (L)	FLRY-B 0.5SQ ORANGE/RED			
COLOR (CODE)	COMPONENT PN (W/O WIRE)	"S" (mm)	"L" (mm)	ELECTRIC WIRE (BASIC/SIDE COLOR)		ASSEMBLY PN (WITH WIRE)		REMARKS	

BLACK (CODE I)	2005339-1	3.5	1550	No. 1 (R)	FLRY-B 0.5SQ YELLOW/ORANGE	2-2005371-5	M300 PAB	A9
				No. 2 (L)	FLRY-B 0.5SQ ORANGE/WHITE			
		4.0	5830	No. 1 (R)	FLRY-B 0.5SQ ORANGE/BLUE	2-2005371-4	J308 CAB RH	A5
				No. 2 (L)	FLRY-B 0.5SQ WHITE/BLACK			
		A8	5880	No. 1 (R)	FLRY-B 0.5SQ ORANGE/GREEN	2-2005371-3	J308 CAB LH	A5
				No. 2 (L)	FLRY-B 0.5SQ VIOLET/ORANGE			
COLOR (CODE)	COMPONENT PN (W/O WIRE)	"S" (mm)	"L" (mm)	ELECTRIC WIRE (BASIC/SIDE COLOR)		ASSEMBLY PN (WITH WIRE)		REMARKS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

SEE TABLE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

AK-II SQUIB PIGTAIL FOR GMK/PACKARD M300/T300/J300/J305/J308/J309

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

SHEET

OF

REV