





LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
A		RELEASED			03.JUL'07	YH	HG	



A-A
SCALE 1:1





POSITION CODIFICATION RIBBING
CABLE HARNESS INTERFACE



ALL CODIFICATION RIBS REALIZED AS INSERT




CODE	A	B	C	D	E	F	G	H	Z
	1,3 5,7	1,4 5,8	2,3 6,7	2,4 6,8	1,3 6,8	2,4 5,7	2,3 5,8	1,4 6,7	NO

* 9 102 060 003 ACCORDING TO CODE Z OF CODIFICATION RIBS





E-E

9 101 090 021	1-2005194-2	X	X	X	0	WITH HOOK	Z
9 102 060 005	2005194-2	X	X	X	X	WITHOUT HOOK	Z
CUSTOMER NO.	TE ASSY NO.	1	2	3	4	OTHER	CODE




NOTE,
1. GENERAL TOLERANCE : ± 0.3 , $\pm 3^{\circ}$

HEADER ASSY P/N	OTHER	WITH HOOK	WITHOUT HOOK
1-2005194-2			
2005194-2			



C-C
SCALE 1:1



13	PRE-TIN	CuSn6	0.63mm TAB(EL)	21	21
12	PRE-TIN	CuSn6	0.63mm TAB(L)	21	21
11	PRE-TIN	CuSn6	0.63mm TAB(M)	21	21
10	PRE-TIN	CuSn6	0.63mm TAB(S)	21	21
9	TINNED	CuSn6	1.5mm TAB(EL)	1	1
8	TINNED	CuSn6	1.5mm TAB(L)	1	1
7	TINNED	CuSn6	1.5mm TAB(M)	1	1
6	TINNED	CuSn6	1.5mm TAB(S)	1	1
5	TINNED	CuSn6	2.8mm TAB(L)	2	2
4	TINNED	CuSn6	2.8mm TAB(M)	2	2
3	TINNED	CuSn6	2.8mm TAB(S)	2	2
2	BLACK	PA66-GF50	JOINT HSG	1	1
1	BLACK	PA66-GF30	HDR HSG(WITH HOOK)	1	1
			HDR HSG(WITHOUT HOOK)	1	1
NO	FINISH/ COLOR	MATERIAL	DESCRIPTION	Q'TY	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN YH MA	AMP KOREA kyungsan, korea	
DIMENSIONS: MM		CHK JV JUNG	NAME	
TO DIMENSIONS UNLESS OTHERWISE SPECIFIED		APVD HG CHD	TCU 94P HEADER ASSY(FOR KEFCO)	
3rd ANGLE PROJECTION		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
SEE NOTE		APPLICATION SPEC	A2 00779 C- 2005194	
MATERIAL		WEIGHT	RESTRICTED TO	
SEE NOTE		CUSTOMER DRAWING	SCALE 1:1 SHEET 1 OF 1 REV A	