








P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED (ECR-23-176535)	25MAY2023	CI	KT



SECTION A—A



P/N	"A"	COLOR	MATERIAL
2005333-3	55	GRAY	PBT-GF15
2005333-2	47	BLACK	PBT-GF15



NOTE.

1. GENERAL TOLERANCES

2. CONDITION OF DELIVERY: DBL PLATE PRE-ASSEMBLY POSITION

3. MATING TORQUE SPEC.: 6 ± 1.0 N.m (0.6 ± 0.1 kgf.cm)


4. APPLIED RECEPTACLE CONTACT P/N:

		PART No.	WIRE SIZE(mm ²)	MATERIAL/FINISH	APPLICATION SPEC	TAB SIZE
△a	SPT 6.3mm	964328-X	2.5~4.0mm ²	-1: CuFe,Pre-Tin	114-18037	6.3 x 0.8t
		964326-X	1.0~2.5mm ²			
		964324-X	0.5~1.0mm ²			
		964322-X	0.2~0.5mm ²			
△b	MT-II 1.5mm	964263-X	0.5~1.0mm ²	-2: CuFe,Pre-Tin -3: CuSn,Contact Area Gold Plated	114-18081	1.6 x 0.6t
		964261-X	0.2~0.5mm ²			
△b	MT-III 1.5mm	1241858-X	0.2~0.5mm ² 1)	-1: CuSn4Pre-Tin -2: CuFe2Pre-Tin 4-1: CuNiSi, Gold Plated	114-18081	1.6 x 0.8t
		1241861-X	0.5~1.0mm ² 1)			

1) Gap Size 0.2mm

LENGTH		UNIT : mm
>=1	<=4	±0.1
>4	<=16	±0.2
>16	<=63	±0.3
>63	<=250	±0.5
>250	<=1000	±0.8

4	STOPPER RING	—	SUS304	1	1
3	M6 BOLT	—	SWCH10A	1	1
2	DBL	NATURAL	PBT	2	2
1	PLUG	GRAY	PBT—GF15	1	—
		BLACK	PBT—GF15	—	1
	NAME	COLOR	MATERIAL	Q'TY	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DH PARK	 TE Connectivity			
		CHK YJ YOUN				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JK SONG	NAME			
	0 PLC ± - 1 PLC SEE NOTE 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	MIXED TIMER 32P PLUG ASSEMBLY			
		APPLICATION SPEC				
		—				
MATERIAL SEE TABLE	FINISH —	WEIGHT 0	SIZE A3	CAGE CODE 00779	DRAWING NO C-2005333	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV A1	