




TAPE MTG DETAIL
SCALE 2:1

- 1 0.76µm [0.000030] MIN PRECIOUS METAL PLATE OVER 1.27µm [0.000050] MIN NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).
- 2 WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
- 1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL—
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
 - 2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER—
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3 OBSOLETE	SMALL PACK	201578-8
	TAPE MTG (SEE DETAIL) 2	201578-4
	STANDARD	201578-1
	PACKAGING TYPE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04/06/93 D.GELTZ		 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK 4-26-93 R.STONE							
		APVD 4-29-93 R.S.KLINE		NAME CONTACT ASSEMBLY, PIN, #16, 20-24 AWG, TYPE II —					
		PRODUCT SPEC —							
		APPLICATION SPEC —							
MATERIAL		WEIGHT —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
PIN BODY: COPPER ALLOY		FINISH		A2	00779	C-201578	—		
PIN BODY: 				CUSTOMER DRAWING					
				SCALE	10:1	SHEET	1 of 1	REV	V