



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
U		REVISED PER ECR-24-213591	28JUN2024	RK	FJS



TAPE MTG DETAIL
SCALE 2:1

1. 0.76µm [.000030] MIN PRECIOUS METAL PLATE OVER 1.27µm [.000050] MIN NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).
2. 2.54µm [.000100] MIN PRECIOUS METAL PLATE OVER 1.27µm [.000050] MIN NICKEL.
3. WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
- 1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
 - 2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	SMALL PACK	1	201580-9	
	TAPE MTG (SEE DETAIL)	2	201580-7	
OBSOLETE	TAPE MTG (SEE DETAIL)	1	201580-4	
	STANDARD	2	201580-3	
	STANDARD	1	201580-1	
PACKAGING TYPE		SOCKET BODY FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ	04/07/93		 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK R.STONE	4-26-93		NAME CONTACT ASSEMBLY, SOCKET, 16, 20-24 AWG, TYPE II —				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.S.KLINE	4-29-93						
		PRODUCT SPEC —							
		APPLICATION SPEC —							
MATERIAL SOCKET BODY: COPPER ALLOY SPRING: STAINLESS STEEL		FINISH SOCKET BODY: SEE TABLE		WEIGHT —		A2	CAGE CODE 00779	DRAWING NO C-201580	RESTRICTED TO —
CUSTOMER DRAWING						SCALE 10:1	SHEET 1 of 1	REV U	