




REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	A1	RELEASEDREVISED PER ECO-15-001494	04FEB2015	AP	DD
	A2	REVISED PER ECN-24-252036	12MAR2024	AP	RS

⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.



⚠ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



NOTCH DESIGNATES
ROW A



UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 03JAN2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 03JAN2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 03JAN2011	NAME	IMPACT, 4 PAIR, 10 COLUMN, HEADER UNGUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH
	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ±	PRODUCT SPEC	SIZE	CAGE CODE DRAWING NO
	ANGLES ±	APPLICATION SPEC	RESTRICTED TO	
MATERIAL	SEE TABLE	WEIGHT	A100779C=2007819	
		CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 2 REV A2

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

	5.5	2007819-3	OBSOLETE
	4.9	2007819-2	
	4.5	2007819-1	
FINISH	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 03JAN2011	 TE Connectivity	
		CHK J. EABY 03JAN2011		
DIMENSIONS:		APVD J. EABY 03JAN2011	NAME	
	mm	PRODUCT SPEC	IMPACT, 4 PAIR, 10 COLUMN, HEADER UNGUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH	
		APPLICATION SPEC		
		WEIGHT		
		CUSTOMER DRAWING		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE		RESTRICTED TO
0 PLC ±		A1		-
1 PLC ±0.25		00779		
2 PLC ±0.13		C=2007819		
3 PLC ±		SCALE		
4 PLC ±		5:1		
ANGLES FINISH		SHEET		
SEE TABLE		2		
-		OF		
-		2		
		REV		
		A2		