




LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	DWN	APVD	
		A	CREATED BY AUTOMATION PROGRAM			02MAY2011	RKC	JE
		A1	REVISED PER ECN-24-252036			10APR2024	AP	RS





- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



288X Ø0.46±0.05
⊕ Ø0.10
PLATED THRU HOLE

UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO 02MAY2011	 TE Connectivity				
DIMENSIONS:		CHK J. EABY 02MAY2011					
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 02MAY2011	NAME IMPACT, 6 PAIR, 16 COLUMN, HEADER UNGUIDED, DUAL END WALL SIGNAL MODULE, 0.46 PTH			
		0 P/LC ± 1 P/LC ±0.25 2 P/LC ±0.13 3 P/LC ± 4 P/LC ± 4 P/LC ANGLES ±	PRODUCT SPEC - APPLICATION SPEC -				
MATERIAL		FINISH SEE TABLE	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			-	A	100779	C=2007898	-
CUSTOMER DRAWING			SCALE	4:1	SHEET	1 OF 2	REV A1

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	SEE SHEET 1	-	-	-	

	5.5	2007898-6	OBSOLETE
	4.9	2007898-5	
	4.5	2007898-4	
	5.5	2007898-3	OBSOLETE
	4.9	2007898-2	
	4.5	2007898-1	
FINISH	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COELLO	02MAY2011	 TE Connectivity					
DIMENSIONS:		CHK J. EABY	02MAY2011						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY	02MAY2011	NAME IMPACT, 6 PAIR, 16 COLUMN, HEADER UNGUIDED, DUAL END WALL SIGNAL MODULE, 0.46 PTH					
		PRODUCT SPEC							
		APPLICATION SPEC							
		MATERIAL		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		-		-		A1	00779	C=2007898	-
		FINISH		CUSTOMER DRAWING		SCALE	5:1	SHEET 2 OF 2	REV A1
		SEE TABLE							