



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	REVISED PER ECR-24-213591	28JUN2024	RK	FJS



0.76μm [0.000030] MIN PRECIOUS METAL PLATE OVER 1.27μm [0.000050] MIN NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).

201334-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.CARBO 20 NOV 97		 TE Connectivity							
		CHK R.STONE 09 DEC 97									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT ASSEMBLY, PIN, #16, 24-28AWG, TYPE II —							
		APVD G.STEINHAUER 16 DEC 97									
		PRODUCT SPEC —									
		APPLICATION SPEC —									
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
SEE CALLOUTS		SEE CALLOUTS		WEIGHT —	A2	00779	C=201334	—			
CUSTOMER DRAWING						SCALE	10:1	SHEET	1 of 1	REV	T