




P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	ADDED UMCC MATING DIM	18MAY2020	CL	SZ
	3	ECR-15-001339	18MAY2020	CL	SZ
	4	ECR-22-136185	18APR2022	JZ	WKH
	A	ECR-22-147664	28JUL2022	JZ	WKH




RECOMMENDED MOUNTING HOLE



- NOTES:
1. MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
 2. SMA BULKHEAD NEED ASSEMBLY NUT AND WASHER
 3. PRODUCT RATING:
TEMPERATURE: -45°C TO +85°C
VOLTAGE: 30V (RMS)
CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
FREQUENCY RANGE: DC TO 9GHz
BEND RADIUS: 5MM MIN
 4. CABLE ASSEMBLY TO BE 100% OPEN AND SHORT TESTED
 5. SMA INTERFACE FOLLOW IEC 60169-15
UMCC IV CAN MATE WITH I-PEX MHF4L SERIES AND HIROSE W.FL SERIES

1-2016694-0	170±3
2016694-9	500±5
2016694-8	450±5
2016694-7	350±5
2016694-6	300±3
2016694-5	250±3
2016694-4	200±3
2016694-3	150±3
2016694-2	100±3
2016694-1	50+3
PART NUMBER	LENGTH

PC	1	HEAT SHRINK TUBE	3
PC	0.5	RF CA,UMCC4 BOTH END, WITH 1.13CABLE	2
PC	1	SMA BULKHEAD, FOR 1.13 CABLE	1
Q'TY	UNIT	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25FEB2019 Cedar Liu	 TE Connectivity	
		CHK 26FEB2019 Roger Song		
DIMENSIONS: mm		APVD Roger Song	NAME RF CA,SMA BULKHEAD TO UMCC GEN4 WITH 1.13 CABLE	
		PRODUCT SPEC -		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	SIZE A3	
0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±-		WEIGHT -		
MATERIAL -		FINISH -	CAGE CODE 00779	
			DRAWING NO C-2016694	
			RESTRICTED TO -	
			SCALE 1:1	
			SHEET 1 OF 1	
			REV A2	