

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	REVISED PER ECR-24-213591	28JUN2024	RK	FJS

D

C

B


A

D

C


B

A




1 0.76µm [0.000030] MIN PRECIOUS METAL PLATE OVER 1.27µm [0.000050] MIN NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).

- 2 WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
- 1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-
 - A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
 - 2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-
 - A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
 - B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL



TAPE MTG DETAIL
SCALE 2:1

TAPE MTD 2	201570-2
STANDARD	201570-1
PACKAGING TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.CARBO 20 NOV 97		 TE Connectivity			
		CHK R.STONE 09 DEC 97					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT ASSEMBLY, PIN, #16, 14AWG, TYPE II —			
		APVD G.STEINHAUER 16 DEC 97					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE CALLOUTS		SEE CALLOUTS		WEIGHT —	A2 00779	C=201570	—
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1	REV T

201570