SPECIFICATION CONTROL DRAWING

2021B3422

CHEMINAX

120 OHM, 0.508 mm2, 19 STRANDS OF .19 mm, TWINAXIAL CABLE, OPTIMIZED DOUBLE SHIELD

7-19-12 Date Revision В

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

CONSTRUCTION DETAILS

ELECTRICAL CHARACTERISTICS

DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED.

CONDUCTORS 0.508 mm², 19 Strands of .0344 .19 mm, Silver-Coated Copper .092 **DIELECTRICS** (nominal) Rayfoam H .094 Colors - Light Blue/White (maximum) **FILLERS** .062 Modified FEP

1ST SHIELD

Silver-Coated Copper,

Silver-Coated Copper,

AWG 38,

Optimized

2ND SHIELD

Optimized

JACKET

Modified FEP

AWG 38,

CHARACTERISTIC IMPEDANCE 120 ± 12 ohms, Method D at 1 MHz

10.5 pF/ft. (nominal) MUTUAL CAPACITANCE **VELOCITY OF PROPAGATION** 75% (nominal)

SURFACE TRANSFER IMPEDANCE 225 milliohms/meter (maximum) from 0.1 to 1000 MHz (Per MIL-DTL-85485)

ADDITIONAL REQUIREMENTS

ELECTRICAL

CONDUCTOR RESISTANCE 11.3 ohms/1000 ft. (nominal)

(prior to cabling)

INSULATION RESISTANCE 10,000 megohms (minimum)

for 1000 ft.

JACKET FLAWS

1.0 kV (rms) SPARK TEST **IMPULSE TEST** 6.0 kV (peak)

VOLTAGE WITHSTAND (DIELECTRIC) 1000 volts (rms) (minimum)

ENVIRONMENTAL

FLAMMABILITY Method B **HEAT SHOCK** 225°C

LOW TEMPERATURE-COLD BEND -55°C/7.00 inch mandrel **VOLTAGE WITHSTAND** 1000 volts (rms), 1 minute

(Post Environmental)

PHYSICAL

INSULATION (DIELECTRIC)

(prior to cabling) 50% (minimum) **ELONGATION** 600 lbf/in2 (minimum) TENSILE STRENGTH

JACKET

ELONGATION 200% (minimum) TENSILE STRENGTH 2000 lbf/in2 (minimum) JACKET THICKNESS .022 inch (nominal)

Outer jacket color will be translucent white (designated by a "-9X" appended to the part number, e.g. 2021B3422-9X) unless

Designate outer jacket color with a dash number in accordance with MIL-STD-681. Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.

58.8 lbs/1000 ft. (nominal) WEIGHT

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

Page 1 of 1

.201

.218

.262

Rayfoam, Cheminax, Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.

