


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	REVISED PER ECR-24-213591	28JUN2024	RK	FJS



- 1

1.27μm [.000050] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 2


0.76μm [.000030] MIN PRECIOUS METAL PLATE IN LOCALIZED PLATE AREA, 0.25μm [.000010] MIN GOLD ON THE REMAINDER ALL OVER
1.27μm [.000050] MIN NICKEL.
CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).
- 3

2.54μm [.000100] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 4

2.54μm [.000100] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.
- 5

1.27μm [.000050] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.

OBSOLETE	4	SMALL PACK	2	202236-8
		STANDARD	2	202236-7
		SMALL PACK	5	202236-6
		STANDARD	5	202236-5
	3	SMALL PACK	1	202236-4
		SMALL PACK	2	202236-3
		STANDARD	1	202236-2
		STANDARD	2	202236-1
	FINISH SOLDER TAB	PACKAGING TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 27SEP90	 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK J.McCLINTON 15DEC90						
		APVD A. BOULLIANNE 15DEC90				NAME PIN ASSEMBLY, LOOSE PIECE, TYPE III+ —		
		PRODUCT SPEC —						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		WEIGHT —	A2	00779	C=202236	—		
MATERIAL SEE CALL OUT	FINISH PIN BODY:SEE TABLE	CUSTOMER DRAWING						
			SCALE	8:1	SHEET	1 of 1		
			REV U					