





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL CREATED	09MAR2020	CL	RS
	A1	ECR-15-001339	18MAY2020	CL	SZ
	A2	ECR-22-136185	18APR2022	JZ	WKH



- NOTES:
1. MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
 2. SMA BULKHEAD NEED ASSEMBLY NUT AND WASHER
 3. PRODUCT RATING:
TEMPERATURE: -45°C TO +85°C
VOLTAGE: 30V (RMS)
CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
FREQUENCY RANGE: DC TO 9GHz
BEND RADIUS: 5MM MIN
 4. CABLE ASSEMBLY TO BE 100% OPEN AND SHORT TESTED
 5. SMA INTERFACE FOLLOW IEC 60169-15
UMCC GEN1 CAN MATE WITH I-PEX MHF SERIES AND HIROSE U.FL SERIES

1-2016682-1	254±3
1-2016682-0	1000±10
2016682-9	750±5
2016682-8	500±5
2016682-7	350±5
2016682-6	300±3
2016682-5	250±3
2016682-4	200±3
2016682-3	150±3
2016682-2	100±3
2016682-1	50+3
PART NUMBER	LENGTH

PC	1	HEAT SHRINK TUBE	3
PC	0.5	RF CA,UMCC GEN1 BOTH END, WITH 1.13CABLE	2
PC	1	SMA BULKHEAD, FOR 1.13 CABLE	1
Q'TY	UNIT	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25MAR2019 Cedar Liu	 TE Connectivity	
		CHK 26MAR2019 Cedar Liu		
DIMENSIONS: mm		APVD 09MAR2020 Roger Song	NAME RF CA,SMA BK TO UMCC GEN1 1.13	
		PRODUCT SPEC	SIZE	
		APPLICATION SPEC	CAGE CODE	
MATERIAL		WEIGHT	DRAWING NO	
-		-	A3 00779	
-		-	C-2016682	
		RESTRICTED CUSTOMER	SCALE 1:1	SHEET 1 OF 1
			REV A2	