

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

	F
--	---

LTR

DESCRIPTION

DATE _____

DWN

APVD

A



RELEASED

14FEB08

J.S

H.K

2023049-1 : AS SHOWN



⑧	GUILDRAIL HOUSING	THERMOPLASTIC MATERIAL UL94V-0	BLACK	1
⑦	BUSH	FREE-CUTTING STEEL	0.005MIN NI PLATING OVER ALL	2
⑥	BRACKET (RIGHT)	STAINLESS STEEL		1
⑤	BRACKET (LEFT)	STAINLESS STEEL		1
④	ARM BAR	STAINLESS STEEL		1
③	SLIDER	STAINLESS STEEL		1
②	UPPER SHELL	STAINLESS STEEL		1
①	PUSH PUSH SUB ASSY			BUTTON COLOR: BLACK
ITEM	NAME	MATERIAL	FINISH / COLOR	Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	02JAN08
-----	---------

CHK	02JAN08
-----	---------

J.LIU	
APVD	02.JAN08

H.KODAMA

PRODUCT SPEC

APPLICATION SPEC



Tyco Electronics

Tyco Electronics Corporation
Taipei, Taiwan

NAME


SHIELD FRAME ASSEMBLY, TOP MOUNT

BUTTON PUSH TYPE, H=5.7

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A 3 00779 C=2023049

DIMENSIONS:
mm



0	PLC	± 0.5
1	PLC	± 0.5
2	PLC	± 0.5
3	PLC	± 0.5
4	PLC	± 0.5

MATERIAL	
----------	--

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
/

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—


2023049-1 : AS SHOWN

VIEW B (TOLERANCE : ±0.05)
REFERENCE P.C.BOARD LAYOUTDETAIL C
REFERENCE P.C.BOARD LAYOUT
(SCALE: 2:1)
(HEADER CONNECTOR MOUNTING LAYOUT DETAIL)

NOTE.

- ① RECOMENDED TIGHTENING TORQUE 0.15~0.2Nm
- ② SCREW LENGTH(FROM MOUNT SURFACE)
- ③ NPTH
- ④ NO COMPONENT AND NO SIGNAL LINE AREA
- ⑤ SOLDERING PAD
- ⑥ GROUNDING PAD
- ⑦ STAND OFF 0
- ⑧ HEADER ASSEMBLY, P/N 2023048-1, PURCHASED SEPARATELY.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.5
2 PLC	± 0.5
3 PLC	± 0.5
4 PLC	± 0.5
ANGLES	± 1°
FINISH	

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation
Taipei, Taiwan

NAME

SHIELD FRAME ASSEMBLY, TOP MOUNT
BUTTON PUSH TYPE, H=5.7
EXPRESS CARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2023049

SCALE NON

SHEET 2 OF 4

REV A

4


3

2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—




REFERENCE FIGURE WHICH ATTACHED
HEADER ASSEMBLY

2023049-1 : AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 Tyco Electronics Tyco Electronics Corporation Taipei, Taiwan				
DIMENSIONS: mm		CHK	NAME				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	SHIELD FRAME ASSEMBLY, TOP MOUNT BUTTON PUSH TYPE, H=5.7 EXPRESS CARD CONNECTOR				
	0 PLC ± 0.5	PRODUCT SPEC					
	1 PLC ± 0.5	APPLICATION SPEC					
	2 PLC ± 0.5						
3 PLC ± 0.5			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
4 PLC ± 0.5			A3	00779	C-2023049	—	
ANGLES ± 1°		WEIGHT					
MATERIAL	FINISH	CUSTOMER DRAWING			SCALE	SHEET	REV
			NON			3 OF 4	A

LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



15	16	240
PCS/TRAY	TRAY/CARTON	TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan			
DIMENSIONS: mm		CHK				
		APVD	NAME SHIELD FRAME ASSEMBLY, TOP MOUNT BUTTON PUST TYPE, H=5.7 EXPRESS CARD CONNECTOR			
		PRODUCT SPEC	SIZE A3			
MATERIAL		APPLICATION SPEC	CAGE CODE 00779			
		WEIGHT	DRAWING NO C-2023049			
		CUSTOMER DRAWING	RESTRICTED TO —			
			SCALE NON			
			SHEET 4 OF 4			
			REV A			