





P	LTR	DESCRIPTION	DATE	DWN	APVD
2		REVISED PER ECR-17-015922	06NOV2017	BDA	KR



- 1
- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
- 2
- SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS (1.0 LBS). NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS (.5 LBS).
- 3
- DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 4
- FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 5
- 150° C TEMPERATURE RATING FOR THIS HOUSING IS FOR SHORT TERM DURATION MAX OPERATING TEMPERATURE REMAINS 125° C.
- 6
- PHOSPHOR BRONZE CONTACTS SHOULD ALWAYS BE USED WITH THIS HOUSING.
- 7
- PRELIMINARY-NOT FOR PRODUCTION.



DETAIL A  
OPTIONAL CONSTRUCTIONS

27.43	1.080
14.73	.580
13.97	.550
11.68	.460
7.62	.300
0.38	.015
0.13	.005
MM	IN
CONVERSION TABLE	

RED	7 2029312-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RACHAVENDRA 29SEP10	 TE Connectivity					
		CHK TOM MICHELUTTI 29SEP10						
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± 0° 30'	APVD TOM MICHELUTTI 29SEP10	NAME					
		PRODUCT SPEC	02P UMNL PLUG HSG,150C-RED					
	MATERIAL NYLON, UL 94V-2, HIGH TEMP	APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT	A1		00779	C2029312	-	
		FINISH		SCALE		SHEET	OF	REV
		CUSTOMER DRAWING		4:1		1	1	2