





152 REF
2 PLC


— OVERMOLDED STRAIN RELIEF
COLOR: BLACK

Obsoleted
Obsoleted
Obsoleted
Obsoleted
Obsoleted



SEE SHEET 2 FOR WIRING SCHEMATIC.

ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF THE CONNECTIVITY SPECIFICATION TEC-138-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SMITH 20APR2009 CHK D.LAWRENCE 20APR2009 APVD D.LAWRENCE 20APR2009		 TE Connectivity Ltd.	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME CABLE ASSY,SFP+ TO SFP+ NI_PLATED —	
MATERIAL —		FINISH —		SIZE A1	
		WEIGHT 0		GAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=2032757	
				RESTRICTED TO —	
				SCALE 1:1 SHEET 1 OF 2 REV H	



REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN
—	—	SEE SHEET 1	—	—

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN T. SMITH 20APR2009		 TE Connectivity Ltd.	
DIMENSIONS: mm		CHK D. LAWRENCE 20APR2009			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 P L C ± -		CABLE ASSY.SFP+ TO SFP+		
	1 P L C ± -		NI_PLATED		
	2 P L C ± -		-		
	3 P L C ± -		RESTRICTED TO		
	4 P L C ± -		-		
	ANGLES		SIZE		
	FINISH		CAGE CODE		
MATERIAL	-	WEIGHT	-	DRAWING NO	-
		CUSTOMER DRAWING		A1 00779 C-2032757	
				SCALE	1:1
				SHEET	2 OF 2
				REV	H