

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



A

RELEASED



13JAN09

FY

WK



RECOMMENDED P.C.B. LAYOUT
TOLERANCE: ±0.05mm



NOTE:

1. MATERIAL:

HOUSING: PA9T WITH 30% GF, UL 94V-0, NATURE COLOR.
CAP: LCP WITH 30% GF, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
TABS: PHOSPHOR BRONZE, 0.25±0.05mm THICKNESS.

2. FINISH:


CONTACTS: 2.54um [100u"] MIN. MATTE-TIN OVER
1.27um [50u"] MIN. NICKEL ON ENTIRE CONTACT.
TABS: 2.54um [100u"] MIN. MATTE-TIN OVER
1.27um [50u"] MIN NICKEL.

3. REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC. 109-201, CONDITION B.

4. NO TE LOGO AND DATE CODE ON THE PRODUCT.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM



MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.35
2 PLC ± 0.25
3 PLC ± -
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE

DWN F. YANG 13JAN2009

CHK S. CHIEN 13JAN2009

APVD W. KODAMA 13JAN2009

PRODUCT SPEC

108-57499

QUALIFICATION TEST REPORT

501-57573

WEIGHT 0.43 GRAMS

CUSTOMER DRAWING



Tyco Electronics Corporation
Taipei, Taiwan

NAME

WTB MALE HEADER,
W/ CAP, P=1.25mm, SMT TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041103

SCALE

SHEET

1 OF 2

REV

A

14

NO. OF
CONTACTS

2041103-1

PART NUMBER

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

44.4

LABEL

ADHESIVE TAPE
4 PLC

160 MIN.

PEELING ANGLE
165° ~ 180°




ø330

ABOUT 160 MM LONG
UNLOADED SECTION

PRODUCT LOADING SECTION

ABOUT 230 MM LONG
UNLOADED SECTION

TOP OF TAPE



1000	4	4000	4.73	1.72	14
PCS/ TAPE	REELS/ CARTON	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	NO. OF CONTACTS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

DIMENSIONS:

MM

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

SEE NOTE

FINISH

SEE NOTE

CHK

APVD

PRODUCT SPEC

QUALIFICATION TEST REPORT

WEIGHT

CUSTOMER DRAWING



Tyco Electronics Corporation

Taipei, Taiwan

NAME

WTB MALE HEADER,
W/ CAP, P=1.25mm, SMT TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041103

SCALE

—

SHEET

2 OF 2

REV

A